


KERN ABJ 80-4NM

The bestseller in analytical balances, with high-quality single-cell weighing system



Units (if device is conformity assessed)	g
--	---

Display

Display type	LCD
Display backlight	no
Display screen size	115×32 mm
Display digit height	14 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	213×333×338 mm
Dimensions rectangular draught shield - inner (W×D×H)	174×162×227 mm
Dimensions rectangular draught shield - outer (W×D×H)	201×220×256 mm
Dimensions weighing surface (Ø)	91 mm
Dimensions weighing surface	91 mm
Material housing	cast aluminium, plastic
Material weighing plate	stainless steel
Material draught shield	glass
Material display housing	Plastics
Level indicator	✓
Levelling feet adjustable	✓

Functions

Sum memory function	✓
Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Underfloor weighing	None
Standby function	✓
Counting function	✓
Counting resolution (laboratory conditions)	82.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Reference quantity	5, 10, 20, 50, 100
Auto-off interval(s) in mains power mode	0 - 99 min
Tare function	manual (multi)
Number of keys for operation	6

Category

Brand	KERN
Product category	Laboratory balance
Product group	Analytical balance
Product family	ABJ

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Single-Cell
Weighing capacity [Max]	82 g
Readability [d]	0,0001 g
Reproducibility	0,0002 g
Linearity	± 0,0003 g
USP Minimum weight of sample (k = 2, U = 0.1%)	400 mg
Resolution	820.000
Adjustment options	Internal calibration (automatic) Adjusting with internal weight (manual)
Automatic adjustment - Standard temperature deviation	2 °C
Automatic adjustment - Standard time interval	4 h
Stabilization time	3 s
Warm-up time	4 h
Eccentric loading at 1/3 [Max]	0,0005 g
Maximum creep (15 minutes)	1 mg
Maximum creep (30 minutes)	2 mg
Default unit	g
Units	g mg

KERN ABJ 80-4NM

The bestseller in analytical balances, with high-quality single-cell weighing system

Interface

Interfaces RS-232 (optional)

Power Supply

Supplied power supply Power supply unit

Plug-in power supply type Power adapter

Plug-in power supply / adapter for countries - included with the delivery

EURO
AUS
UK
US
CH

Plug-in power supply / adapter for countries - optional

EURO
AUS
UK
US
CH

Input voltage power supply / power [Max] 110 V - 230 V AC

Input voltage device / power [Max] 12 V DC, 1000 mA

Environmental conditions

Ambient temperature [Min] 10 °C

Ambient temperature [Max] 30 °C

Humidity of environment [Min] 20 %

Humidity of environment [Max] 85 %

Storage temperature [Min] -10 °C

Storage temperature [Max] 50 °C

Approval

CE mark ✓

Services (optional)

Article number for DAkkS calibration 963-101

Article number for certificate of conformity 969-517

Packing & Shipping

Delivery time 1 d

Dimensions packaging (W×D×H) 395×565×530 mm

Shipping method Parcel service


Net weight approx. 7 kg

Gross weight approx. 9 kg

Shipping weight 23,7 kg

Pictograms

STANDARD



OPTION

