

# KERN BSWA-01

Adjustment device for regular adjustment of the sound level meter



## Approval

CE mark ✓

## Services (optional)

Article number for DAkkS calibration 963-291

Article number for factory calibration 961-291

## Packing & Shipping

Delivery time 1 d  
Dimensions packaging (W×D×H) 145×105×70 mm  
Net weight 0,06 kg  
Shipping method Parcel service  
Net weight approx. 0,10 kg  
Gross weight approx. 0,25 kg  
Shipping weight 0,245 kg

## Pictograms

### STANDARD



## Category

Brand Sauter  
Product category Measurementtechnology

## Measuring System

Frequency range [Min] 990 Hz  
Frequency range [Max] 1010 Hz  
Sound level [Min] (db) 94 dB  
Sound level [Max] (db) 114 dB  
Sound level meter class Class 1  
Class 2  
Units dB  
Tolerance (% of [Max]) 0,2%

## Construction

Dimension housing (W×D×H) 70×70×50 mm  
Dimensions completely mounted (W×D×H) 70×70×50 mm  
Material housing plastic

## Power Supply

Supplied power supply Battery  
Battery / accumulator type Alkali(-Manganese)  
Battery connection Pad + Spring  
Battery capacity 3.000 mAh  
Battery voltage 3 V

## Environmental conditions

Use temperature [Min] -10 °C  
Use temperature [Max] 50 °C  
Storage temperature [Min] -10 °C  
Storage temperature [Max] 60 °C