



**CB Q1 · CB Q2**  
**Bending beam and shear beam load cell made of stainless steel**

**Technical data**

- Accuracy in accordance with OIML R60 C3
- CE and RoHS compliant
- Protection against dust and water splashes IP68/IP69K (in accordance with EN 60529), welded to create a hermetic seal
- Stainless steel
- Area of application: Measuring mass as well as compressive force in harsh environments
- Suitable for platform scales, weigh hoppers, floor scales and other weighing devices
- 4-wire connection
- Nominal sensitivity: 2 mV/V
- Cable length: 3 m
- Accuracy class OIML R60 C6 or EX version on request

**CB P1**  
**Bending beam made of nickel-plated steel**

**Technical data**

- Accuracy in accordance with OIML R60 C3
- CE and RoHS compliant
- Protection against dust and water splashes IP67 (in accordance with EN 60529), hermetically encapsulated
- Nickel-plated steel
- Area of application: Measuring mass as well as compressive force in harsh environments
- Suitable for platform scales, silo scales, bed scales and other types of scales
- 4-wire connection
- Nominal sensitivity: 3 mV/V
- Cable length: 3 m

Discover more details and matching accessories online!

STANDARD

IP 68 IP 69K 1 DAY

OPTION

DAkkS ISO

[Max] ≤ 500 kg

STANDARD

IP 67 M 1 DAY

OPTION

DAkkS ISO

| Model        | Nominal load | Price<br>excl. of VAT<br>ex works |
|--------------|--------------|-----------------------------------|
| SAUTER       | kg           | €                                 |
| CB 5-3Q1     | 5            | 230,-                             |
| CB 10-3Q1    | 10           | 230,-                             |
| CB 20-3Q1    | 20           | 230,-                             |
| CB 30-3Q1    | 30           | 230,-                             |
| CB 50-3Q1    | 50           | 230,-                             |
| CB 75-3Q1    | 75           | 230,-                             |
| CB 100-3Q1   | 100          | 230,-                             |
| CB 150-3Q1   | 150          | 230,-                             |
| CB 200-3Q1   | 200          | 230,-                             |
| CB 250-3Q1   | 250          | 230,-                             |
| CB 300-3Q1   | 300          | 230,-                             |
| CB 500-3Q1   | 500          | 230,-                             |
| CB 750-3Q2*  | 750          | 240,-                             |
| CB 1000-3Q2* | 1000         | 240,-                             |
| CB 1500-3Q2* | 1500         | 240,-                             |

| Model      | Nominal load |
|------------|--------------|
| SAUTER     | kg           |
| CB 100-3P1 | 100          |
| CB 250-3P1 | 250          |

\* ONLY WHILE STOCKS LAST