

KERN CB 750-3Q2

KERN

Bending beam and shear beam load cell made from stainless steel



Dimension (Ø×H)	50×136,5 mm
Material	stainless steel
Cable length	3 m
Mounting - force dissipation	2 × through hole Ø 13 mm
Mounting - force application	Through-hole Ø 13 mm

Functions

IP protection - complete device	IP68
---------------------------------	------

Environmental conditions

Ambient temperature [Min]	-30 °C
Ambient temperature [Max]	70 °C
Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	250×155×60 mm
Net weight	0,454 kg
Shipping method	Parcel service
Net weight approx.	0,50 kg
Gross weight approx.	0,70 kg
Shipping weight	0,687 kg

Pictograms

STANDARD



OPTION



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CB Q2

Measuring System

Weighing capacity [Max]	750 kg
Directions of force	compression
Load cell connection	4-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Load cell - characteristic value - nominal	2 mV/V
Load cell - characteristic value - variance	0,002 mV/V
Load cell - Y-value	10000
Load cell - Combined error	0,017%
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Load cell - Input resistance - nominal	400 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Isolation resistance - [Min]	5000 MΩ
Load cell - Recommended excitation voltage [Min]	10 V
Load cell - Recommended excitation voltage [Max]	15 V
Load cell - Input resistance - variance	20 Ω
Load cell - Output resistance - variance	3 Ω

Construction

Design	bending beam
--------	--------------