

KERN CCS 150K0.1.

Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999



Display	
Display type	LCD
Display backlight	✓
Display digit height	20 mm

Construction	
Dimensions completely mounted (W×D×H)	320×350×125 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×124 mm
Material housing	plastic
Material weighing plate	stainless steel
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Cable length	1,5 m
Display device cable length	3 m

Functions	
PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Conversion function	✓
PLU - total	100
Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Underfloor weighing	None
Counting function	✓
Counting resolution (laboratory conditions)	1.500.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	n (any number of pieces)
IP protection - display	IP23
IP protection - platform	IP65
IP protection - load cell	IP65
Memory function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Tare function	manual (multi)
Number of keys for operation	20

Category	
Brand	KERN
Product category	Industrial scale
Product group	Counting system
Product family	CCS

Measuring System	
Reference scale - item number	CFS 6K0.1
Quantity scale - Item number	TKFP 150V20M-A
Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Reference scale - Weighing capacity [Max]	6 kg
Quantity scale - Weighing capacity [Max]	150 kg
Quantity scale - Readability [d]	0,005 kg
Reference scale - Readability [d]	100 mg
Reproducibility	0,0002 kg
Reference scale - Reproducibility	100 mg
Quantity scale - Reproducibility	0,005 kg
Linearity	±
Reference scale - Linearity	200 mg
Quantity scale - Linearity	0,02 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Stabilization time	2 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,0004 kg
Reference scale - Eccentric loading at 1/3 [Max]	500 mg
Quantity scale - Eccentric loading at 1/3 [Max]	0,025 kg
Default unit	kg
Units	kg lb
Loadcell type	aluminum Alloy IP64

KERN CCS 150K0.1.



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999

Interface

Interfaces	RS-232 standard
------------	-----------------

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH

Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
---	-------------------------------

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
--	-------------------------

Input voltage device / power [Max]	12 V, 500 mA
------------------------------------	--------------

Rechargeable battery	GAB-A04
----------------------	---------

Rechargeable battery operating time - backlight on	70 h
--	------

Rechargeable battery operating time - backlight off	60 h
---	------

Rechargeable battery charging time	12 h
------------------------------------	------

Rechargeable battery optional	Rchrg. battery optional
-------------------------------	-------------------------

Environmental conditions

Ambient temperature [Min]	0 °C
---------------------------	------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Min]	0 %
-------------------------------	-----

Humidity of environment [Max]	80 %
-------------------------------	------

Storage temperature [Min]	-20 °C
---------------------------	--------

Storage temperature [Max]	60 °C
---------------------------	-------

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	abhängig von Auflösung/ Max depends on resolution and capacity
---	--

Article number for DAkkS calibration	962-129-128
--------------------------------------	-------------

Article number for certificate of conformity	969-517
--	---------

Packing & Shipping

Delivery time	2 d
---------------	-----

Dimensions packaging (W×D×H)	1010×650×230 mm
------------------------------	-----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	16 kg
--------------------	-------

Gross weight approx.	20 kg
----------------------	-------

Shipping weight	30,2 kg
-----------------	---------

Pictograms

STANDARD



OPTION

