

# KERN CCS 150K0.1.

Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999



## Display

Display type	LCD
Display backlight	✓
Display digit height	20 mm

## Construction

Dimensions completely mounted (W×D×H)	320×350×125 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×124 mm
Material housing	plastic
Material weighing plate	stainless steel
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Cable length	1,5 m
Display device cable length	3 m

## Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Conversion function	✓
PLU - total	100
Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Underfloor weighing	None
Counting function	✓
Counting resolution (laboratory conditions)	1.500.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	n (any number of pieces)
IP protection - display	IP23
IP protection - platform	IP65
IP protection - load cell	IP65
Memory function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Tare function	manual (multi)
Number of keys for operation	20

## Category

Brand	KERN
Product category	Industrial scale
Product group	Counting system
Product family	CCS

## Measuring System

Weighing system	Strain gauge
Reference scale - Weighing capacity [Max]	6 kg
Reproducibility	0,0002 kg
Linearity	±
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Quantity scale - Item number	TKFP 150V20M-A
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,0004 kg
Reference scale - Eccentric loading at 1/3 [Max]	500 mg
Quantity scale - Linearity	0,02 kg
Quantity scale - Eccentric loading at 1/3 [Max]	0,025 kg
Quantity scale - Reproducibility	0,005 kg
Reference scale - Reproducibility	100 mg
Reference scale - item number	CFS 6K0.1
Reference scale - Linearity	200 mg
Construction type of the scale	Multi-range balance
Units	kg lb
Default unit	kg
Loadcell type	aluminum Alloy IP64
Quantity scale - Readability [d]	0,005 kg
Quantity scale - Weighing capacity [Max]	150 kg
Reference scale - Readability [d]	100 mg

# KERN CCS 150K0.1.

# KERN

Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999

## Interface

Interfaces	RS-232 standard
------------	-----------------

## Power Supply

Supplied power supply	Power supply unit
-----------------------	-------------------

Power supply type	Power adapter
-------------------	---------------

Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH

Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US
	CH

Power supply - Cable length	180 cm
-----------------------------	--------

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
--	-------------------------

Input voltage device / power [Max]	12 V, 500 mA
------------------------------------	--------------

Power socket for mains adapter	Inside plus, outside minus
--------------------------------	----------------------------

Rechargeable battery	GAB-A04
----------------------	---------

Rechargeable battery operating time - backlight on	70 h
--	------

Rechargeable battery operating time - backlight off	60 h
---	------

Rechargeable battery charging time	12 h
------------------------------------	------

Rechargeable battery optional	Rchrg. battery optional
-------------------------------	-------------------------

## Environmental conditions

Ambient temperature [Min]	0 °C
---------------------------	------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Min]	0 %
-------------------------------	-----

Humidity of environment [Max]	80 %
-------------------------------	------

Storage temperature [Min]	-20 °C
---------------------------	--------

Storage temperature [Max]	60 °C
---------------------------	-------

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for adjustment at the location of installation	abhängig von Auflösung/ Max   depends on resolution and capacity
---	--

Article number for DAkkS calibration	962-129-128
--------------------------------------	-------------

Article number for certificate of conformity	969-517
--	---------

## Packing & Shipping

Delivery time	2 d
---------------	-----

Dimensions packaging (W×D×H)	1010×650×230 mm
------------------------------	-----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	16 kg
--------------------	-------

Gross weight approx.	20 kg
----------------------	-------

Shipping weight	30,2 kg
-----------------	---------

Shipping volume weight	30,2 kg
------------------------	---------

## Product information

GTIN/EAN number	404576 1153264
-----------------	----------------

Trade number	84238220
--------------	----------

REACH classification	no prohibited substances
----------------------	--------------------------

## Pictograms

### STANDARD



### OPTION

