


SAUTER CE HSN



Compact display device (rail-mounted module) for installation in switch cabinets



Interface

Interfaces	Digital I/O RS-485 USB-Device Profinet
------------	---

Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	70 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	auf Anfrage on request
---	--------------------------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	260×155×140 mm
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,45 kg
Shipping weight	1,1 kg

Pictograms

STANDARD



Category

Brand	Sauter
Product category	Measuring Technology Component
Product group	Digital weighing transmitter
Product family	CE HS

Measuring System

Terminal resolution (not verifiable)	10.000
Adjustment options	Adjusting with external weight
Internal measuring frequency	1600 Hz
Number of platforms / channels	1
Load cell - load cell resistance [Min] (Ohm)	43,75
Load cell - load cell resistance [Max] (Ohm)	1200
Load cell connection	6-wire

Display

Display type	7 segment LED
Display segments	6
Display digit height	7,62 mm

Construction

Dimension display device (W×D×H)	120×101×23 mm
----------------------------------	---------------

Functions

IP protection - complete device	IP20
Tare function	automatic & manual (multi)
Number of keys for operation	3