

# SAUTER CE P30110

Gap for shear beam loadcell

**KERN**



## Category

Brand	Sauter
Product category	Measurementtechnology
Product group	Load cell accessories

## Construction

Dimensions completely mounted (W×D×H)	102×51×4 mm
Material	steel, nickel-plated

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	120×100×80 mm
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,25 kg
Shipping weight	0,25 kg

## Pictograms

### STANDARD

