


SAUTER CK 50-Y4

KERN

Flat miniature alloy steel load cell



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CK Y4

Measuring System

Weighing capacity [Max]	50 kg
Directions of force	compression
Load cell connection	4-wire
Load cell OIML class	C1
Load cell - characteristic value - nominal	0,8 mV/V
Load cell - characteristic value - variance	0,2 mV/V
Load cell - Combined error	0,05%
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Load cell - Input resistance - nominal	1000 Ω
Load cell - Output resistance - nominal	1000 Ω
Load cell - Isolation resistance - [Min]	2000 M Ω
Load cell - Recommended excitation voltage [Min]	9 V
Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Input resistance - variance	10 Ω
Load cell - Output resistance - variance	10 Ω

Construction

Design	Miniature bending beam
Dimension (W×D×H)	34×34×4,5 mm

Material	steel, galvanized
Cable length	0,45 m
Mounting - force dissipation	4 × through hole \varnothing 3,1 mm
Mounting - force application	Support point

Functions

IP protection - complete device	IP65
---------------------------------	------

Environmental conditions

Ambient temperature [Min]	-20 °C
Ambient temperature [Max]	50 °C
Use temperature [Min]	-10 °C
Use temperature [Max]	60 °C
Storage temperature [Min]	-30 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration (compressive force)	963-261V
--	----------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	490×34×4 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg

Pictograms

STANDARD

