

# SAUTER CP 100-3-3Y1

Single-point load cell made of anodised aluminium



## Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CP Y1

## Measuring System

Weighing capacity [Max]	100 kg
Directions of force	compression
Load cell connection	4-wire
Load cell OIML class	C3
Load cell - characteristic value - nominal	2 mV/V
Load cell - characteristic value - variance	0,2 mV/V
Load cell - Combined error	0,03%
Load cell - Dead load [Min] (%)	0%
Load cell - Input resistance - nominal	405 $\Omega$
Load cell - Output resistance - nominal	350 $\Omega$
Load cell - Isolation resistance - [Min]	5000 M $\Omega$
Load cell - Input resistance - variance	10 $\Omega$
Load cell - Output resistance - variance	3 $\Omega$

## Construction

Design	Singlepoint load cell
Dimension (W×D×H)	130×22×30 mm
Material	aluminium
Cable length	3 m
Mounting - force dissipation	2 × threaded hole M6
Mounting - force application	2 × threaded hole M6
Maximum platform size	250×350 mm

## Functions

IP protection - complete device	IP65
---------------------------------	------

## Environmental conditions

Ambient temperature [Min]	-20 °C
Ambient temperature [Max]	50 °C
Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Storage temperature [Min]	-30 °C
Storage temperature [Max]	60 °C

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for DAkkS calibration (compressive force)	963-261V
--	----------

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	120×50×35 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg

## Pictograms

### STANDARD



### OPTION

