

SAUTER CP 150-3P2

Single-point load cell made of aluminium

KERN



Dimension (W×D×H)	150×35×40 mm
Material	aluminium
Cable length	2 m
Mounting - force dissipation	4 × threaded hole M6
Mounting - force application	4 × threaded hole M6
Maximum platform size	400×400 mm

Functions

IP protection - complete device	IP65
---------------------------------	------

Environmental conditions

Ambient temperature [Min]	-35 °C
Ambient temperature [Max]	65 °C
Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Storage temperature [Min]	-40 °C
Storage temperature [Max]	70 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration (compressive force)	963-262V
--	----------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	160×110×110 mm
Shipping method	Parcel service
Net weight approx.	0,60 kg
Gross weight approx.	0,65 kg
Shipping weight	0,612 kg

Pictograms

STANDARD



OPTION



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CP P2

Measuring System

Weighing capacity [Max]	150 kg
Directions of force	compression
Load cell connection	4-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Load cell - characteristic value - nominal	2 mV/V
Load cell - characteristic value - variance	0,2 mV/V
Load cell - Y-value	10000
Load cell - Combined error	0,023%
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Load cell - Input resistance - nominal	406 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Isolation resistance - [Min]	5000 MΩ
Load cell - Recommended excitation voltage [Min]	5 V
Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Input resistance - variance	6 Ω
Load cell - Output resistance - variance	3 Ω

Construction

Design	Singlepoint load cell
--------	-----------------------