

# SAUTER CP 40-3P3

# KERN

Single-point load cell made of anodised aluminium



## Construction

Design	Singlepoint load cell
Dimension (W×D×H)	150×25,4×40 mm
Material	aluminium
Cable length	3 m
Mounting - force dissipation	2 × threaded hole M6
Mounting - force application	2 × threaded hole M6
Maximum platform size	350×400 mm

## Functions

IP protection - complete device	IP65
---------------------------------	------

## Environmental conditions

Ambient temperature [Min]	-35 °C
Ambient temperature [Max]	65 °C
Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Storage temperature [Min]	-40 °C
Storage temperature [Max]	70 °C

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for DAkkS calibration (compressive force)	963-261V
--	----------

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	225×115×35 mm
Shipping method	Parcel service
Net weight approx.	0,40 kg
Gross weight approx.	0,45 kg
Shipping weight	0,439 kg

## Pictograms

### STANDARD



### OPTION



## Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CP P3

## Measuring System

Weighing capacity [Max]	40 kg
Directions of force	compression
Load cell connection	6-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Load cell - characteristic value - nominal	2 mV/V
Load cell - characteristic value - variance	0,2 mV/V
Load cell - Y-value	12000
Load cell - Combined error	0,023%
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Load cell - Input resistance - nominal	409 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Isolation resistance - [Min]	5000 MΩ
Load cell - Recommended excitation voltage [Min]	5 V
Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Input resistance - variance	6 Ω
Load cell - Output resistance - variance	3 Ω