

# KERN CPB 30K5DM

Professional model, also with EC type approval [M], counting resolution up to 60,000 points



## Construction

Dimension housing (W×D×H)	315×350×100 mm
Dimensions device (W×D×H)	315×350×125 mm
Dimensions completely mounted (W×D×H)	315×350×125 mm
Dimensions weighing surface (W×D)	295×225 mm
Dimensions weighing surface	295×225 mm
Material housing	plastic
Material weighing plate	stainless steel
Level indicator	✓
Levelling feet adjustable	✓

## Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	None
Counting function	✓
Counting resolution (laboratory conditions)	60.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	500 mg
Smallest piece weight when piece counting - normal conditions	5 g
Reference quantity	n (any number of pieces)
	3 min
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 30 min 15 min
Tare function	manual (single & multi)
Number of keys for operation	20

## Interface

Interfaces	RS-232 standard
------------	-----------------

## Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH

## Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	CPB

## Measuring System

Construction type of the scale	Multi-division balance
Weighing system	Strain gauge
Weighing capacity [Max]	15 kg; 30 kg
Readability [d]	0,005 kg; 0,01 kg
Reproducibility	0,005 kg; 0,01 kg
Linearity	± 0,01 kg; 0,02 kg
Minimum weight [Min]	0,1 kg
Resolution	3.000, 3.000
Tare range	29,99 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	20 kg (F2); 10 kg (F2)
Possible calibration points	15 kg; 30 kg
Stabilization time	2 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	0,02 kg; 0,05 kg
Default unit	kg
Units	kg

## Display

Display type	LCD
Display backlight	✓
Display digit height	20 mm

# KERN CPB 30K5DM

# KERN

Professional model, also with EC type approval [M], counting resolution up to 60,000 points

Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Rechargeable battery	GAB-A04
Rechargeable battery operating time - backlight on	50 h
Rechargeable battery operating time - backlight off	90 h
Rechargeable battery charging time	12 h
Rechargeable battery optional	Rchrg. battery optional - intern

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	0,005 kg; 0,01 kg

## Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	445×375×220 mm
Shipping method	Parcel service
Net weight approx.	3,6 kg
Gross weight approx.	4,4 kg

Shipping weight 7,3 kg

## Pictograms

### STANDARD



### OPTION



### FACTORY

