

KERN CPB 6K1DM

Professional model, also with EC type approval [M], counting resolution up to 60,000 points



Construction

Dimension housing (W×D×H)	315×350×100 mm
Dimensions device (W×D×H)	315×350×125 mm
Dimensions completely mounted (W×D×H)	315×350×125 mm
Dimensions weighing surface (W×D)	295×225 mm
Dimensions weighing surface	295×225 mm
Material housing	plastic
Material weighing plate	stainless steel
Level indicator	✓
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,1 Nm

Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	None
Counting function	✓
Counting resolution (laboratory conditions)	60.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	n (any number of pieces)
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 30 min 15 min
Tare function	manual (single & multi)
Number of keys for operation	20

Interface

Interfaces	RS-232 standard
------------	-----------------

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH

Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	CPB

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	3 kg; 6 kg
Readability [d]	0,001 kg; 0,002 kg
Reproducibility	0,001 kg; 0,002 kg
Linearity	± 0,002 kg; 0,004 kg
Minimum weight [Min] (verifiable)	0,02 kg
Resolution	3.000, 3.000
Tare range	5,998 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	5 kg (F2); 1 kg (F2)
Possible calibration points	3 kg; 6 kg
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,005 kg; 0,01 kg
Construction type of the scale	Multi-division balance
Units	kg
Default unit	g

Display

Display type	LCD
Display backlight	✓
Display digit height - smallest digit	4 mm
Display digit height	20 mm

KERN CPB 6K1DM

KERN

Professional model, also with EC type approval [M], counting resolution up to 60,000 points

Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Power supply - Cable length	180 cm
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
Rechargeable battery	GAB-A04
Rechargeable battery operating time - backlight on	50 h
Rechargeable battery operating time - backlight off	90 h
Rechargeable battery charging time	12 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	0,001 kg; 0,002 kg

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	450×375×220 mm
Shipping method	Parcel service
Net weight approx.	3,4 kg
Gross weight approx.	4,4 kg
Shipping weight	7,4 kg
Shipping volume weight	7,4 kg

Product information

GTIN/EAN number	404576 1124363
Trade number	84238 129
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



FACTORY

