

# KERN CXB 30K10NM

# KERN

Entry level model into professional counting, counting resolution of 30,000 points, verification optional



## Construction

Dimension housing (W×D×H)	300×330×110 mm
Dimensions weighing surface (W×D)	300×225 mm
Dimensions weighing surface	300×225 mm
Material housing	plastic
Material weighing plate	stainless steel
Level indicator	✓
Levelling feet adjustable	✓

## Functions

Recipe/summing level	Rez A (Net total)
Tolerance weighing - type of signal	acoustically
Underfloor weighing	None
Counting function	✓
Counting resolution (laboratory conditions)	30.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Reference quantity	n (any number of pieces)
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Tare function	manual (multi)
Number of keys for operation	20

## Power Supply

Supplied power supply	Accu & Power supply
Plug-in power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	UK CH
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Battery / accumulator type	Pb
Battery connection	Plug-in terminals
Rechargeable battery	6 V, 4 Ah
Rechargeable battery operating time - backlight on	60 h
Rechargeable battery operating time - backlight off	200 h
Rechargeable battery charging time	8 h

## Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	CXB

## Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	30000 g
Readability [d]	10 g
Reproducibility	10 g
Linearity	± 20 g
Minimum weight [Min]	200 g
Resolution	3.000
Tare range	30000 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	20 kg (M1); 10 kg (M1)
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	30 g
Default unit	g
Units	kg g
Units (if device is conformity assessed)	g

## Display

Display type	LCD
Display backlight	✓
Display digit height	18 mm

# KERN CXB 30K10NM



Entry level model into professional counting, counting resolution of 30,000 points, verification optional

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	15 %
Humidity of environment [Max]	85 %

## Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	10 g

## Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	375×395×175 mm
Net weight	4 kg
Shipping method	Parcel service
Net weight approx.	4,0 kg
Gross weight approx.	4,4 kg
Shipping weight	5,2 kg

## Pictograms

### STANDARD



### OPTION



### FACTORY

