

KERN DE 150K20D

Versatile, successful model with stainless steel platform for flexible use



Default unit	kg
--------------	----

Display

Display type	LCD
Display backlight	✓
Display screen size	87×29 mm
Display digit height	25 mm

Construction

Dimension housing (W×D×H)	315×305×75 mm
Dimension display device (W×D×H)	225×110×55 mm
Dimensions weighing surface (W×D)	318×308 mm
Dimensions weighing surface	318×308 mm
Dimensions weighing platform (W×D×H)	318×308×75 mm
Material weighing plate	stainless steel
Material platform	metal, lacquered
Material display housing	plastic
Display device cable length	1,5 m
Allowed cable length display device [Max]	3 m
Load cells - number	4

Functions

Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Underfloor weighing	None
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	7.500
Smallest piece weight when piece counting - laboratory conditions	20 g
Smallest piece weight when piece counting - normal conditions	200 g
Reference quantity	5, 10, 20, 25, 50
IP protection - display	no IP protection
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off
Tare function	manual (multi)
Number of keys for operation	5

Interface

Interfaces	RS-232 standard
------------	-----------------

Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	DE

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	60 kg; 150 kg
Readability [d]	0,02 kg; 0,05 kg
Reproducibility	0,02 kg; 0,05 kg
Linearity	± 0,06 kg; 0,15 kg
Resolution	3.000, 3.000
Tare range	150 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Possible calibration points	50 kg; 100 kg; 150 kg
Stabilization time	2,5 s
Eccentric loading at 1/3 [Max]	0,1 kg; 0,25 kg
Construction type of the scale	Multi-division balance

Units	kg
	dwt
	tl (Tw)
	tl (HK)
	ozt
	mo
	lb
	oz
	ffa
	tol

Maximum creep (15 minutes)	200 g
----------------------------	-------

Maximum creep (30 minutes)	400 g
----------------------------	-------

KERN DE 150K20D

KERN

Versatile, successful model with stainless steel platform for flexible use

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
CH	
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	15 V, 500 mA
Power socket for mains adapter	Double plug, left minus, right plus, 14,3 mm × 6,1 mm long 47,5 mm
Battery / accumulator type	NiMH
Battery	9 V block
Battery connection	Plug-in terminals
Battery operating time	12 h
Rechargeable battery	NDE-A02
Rechargeable battery operating time - backlight on	15 h
Rechargeable battery operating time - backlight off	30 h
Rechargeable battery charging time	10 h
Rechargeable battery optional	Rchrg. battery optional

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	515×385×135 mm
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	6 kg
Shipping weight	5,8 kg
Shipping volume weight	5,4 kg

Product information

GTIN/EAN number	4045761111158
Trade number	84238220
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

