

KERN DE 150K20DL

The long lasting story of success with dust and spray protected display device



ffa
tol

Display

Display type	LCD
Display backlight	✓
Display screen size	87×29 mm
Display digit height	25 mm

Construction

Dimension display device (W×D×H)	225×110×55 mm
Dimensions weighing surface (W×D)	522×403 mm
Dimensions weighing surface	522×403 mm
Dimensions weighing platform (W×D×H)	522×403×83 mm
Material weighing plate	stainless steel
Material platform	metal, lacquered
Material display housing	Plastics
Display device cable length	1,5 m
Allowed cable length display device [Max]	3 m
Load cells - number	4

Functions

Recipe/summing level	Sum A
Percentage determination	✓
Underfloor weighing	None
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	3.750
Smallest piece weight when piece counting - laboratory conditions	40 g
Smallest piece weight when piece counting - normal conditions	400 g
Reference quantity	5, 10, 20, 25, 50
IP protection - display	no IP protection
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	5

Interface

Interfaces	RS-232 standard
------------	-----------------

Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	DE

Measuring System

Construction type of the scale	Multi-division balance
Weighing system	Strain gauge
Weighing capacity [Max]	60 kg; 150 kg
Readability [d]	0,02 kg; 0,05 kg
Reproducibility	0,02 kg; 0,05 kg
Linearity	± 0,06 kg; 0,15 kg
Resolution	3.000, 3.000
Tare range	150 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Possible calibration points	50 kg; 100 kg; 150 kg
Stabilization time	2,5 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	0,1 kg; 0,25 kg
Maximum creep (15 minutes)	200 g
Maximum creep (30 minutes)	400 g
Default unit	kg

Units

kg
dwt
tl (Tw)
tl (HK)
ozt
mo
lb
oz

KERN DE 150K20DL

KERN

The long lasting story of success with dust and spray protected display device

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	15 V, 500 mA
Battery / accumulator type	NiMH
Battery	9 V block
Battery connection	Plug-in terminals
Battery operating time	12 h
Rechargeable battery	PCB-A01
Rechargeable battery operating time - backlight on	15 h
Rechargeable battery operating time - backlight off	30 h
Rechargeable battery charging time	10 h
Rechargeable battery optional	Rchrg. battery optional

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129
Article number for certificate of conformity	969-517


Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	620×600×190 mm

Shipping method	Parcel service
Net weight approx.	16 kg
Gross weight approx.	18 kg
Shipping weight	17,7 kg

Pictograms

STANDARD



OPTION

