

KERN DE 6K0.5A

The long lasting story of success with dust and spray protected display device



oz
ffa
tol

Display	
Display type	LCD
Display backlight	✓
Display screen size	87×29 mm
Display digit height	25 mm

Construction	
Dimension housing (W×D×H)	310×300×75 mm
Dimension display device (W×D×H)	225×110×55 mm
Dimensions weighing surface (W×D)	318×308 mm
Dimensions weighing surface	318×308 mm
Dimensions weighing platform (W×D×H)	318×308×75 mm
Material weighing plate	stainless steel
Material platform	metal, lacquered
Material display housing	Plastics
Display device cable length	1,4 m
Allowed cable length display device [Max]	3 m
Load cells - number	4

Functions	
Recipe/summing level	Sum A
Percentage determination	✓
Underfloor weighing	None
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	6.000
Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Reference quantity	5, 10, 20, 25, 50
IP protection - display	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off
Tare function	manual (multi)
Number of keys for operation	5

Interface	
Interfaces	RS-232 standard

Category	
Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	DE

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	6000 g
Readability [d]	0,5 g
Reproducibility	0,5 g
Linearity	± 1,5 g
Resolution	12.000
Tare range	6000 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6 kg (M1)
Possible calibration points	2 kg; 4 kg; 6 kg
Stabilization time	2,5 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	2,5 g
Maximum creep (15 minutes)	2 g
Maximum creep (30 minutes)	4 g
Default unit	g

	kg
	g
	dwt
Units	tl (Tw)
	tl (HK)
	ozt
	mo
	lb

KERN DE 6K0.5A

KERN

The long lasting story of success with dust and spray protected display device

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	15 V, 500 mA
Battery / accumulator type	NiMH
Battery	9 V block
Battery connection	Plug-in terminals
Battery operating time	12 h
Rechargeable battery	NDE-A02
Rechargeable battery operating time - backlight on	15 h
Rechargeable battery operating time - backlight off	30 h
Rechargeable battery charging time	10 h
Rechargeable battery optional	Rchrg. battery optional

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517


Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	517×390×135 mm

Net weight	4,78 kg
Shipping method	Parcel service
Net weight approx.	4,8 kg
Gross weight approx.	6 kg
Shipping weight	5,58 kg

Pictograms

STANDARD



OPTION

