

KERN ECB 10K-3N

KERN

Plain, mobile, uncomplicated



Category

Brand	KERN
Product category	Industrial scale
Product group	Bench scale
Product family	ECB

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	10 kg
Readability [d]	0,005 kg
Reproducibility	0,005 kg
Linearity	± 0,02 kg
Resolution	2.000
Tare range	10 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	5 kg (M3)
Possible calibration points	5 kg
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,015 kg
Maximum creep (15 minutes)	10 g
Maximum creep (30 minutes)	20 g
Default unit	kg
Units	kg

Display

Display type	LCD
Display backlight	✓
Display screen size	100×25 mm
Display digit height	21 mm

Construction

Dimension housing (W×D×H)	320×300×60 mm
---------------------------	---------------

Dimensions weighing surface (W×D)	320×260 mm
Dimensions weighing surface	320×260 mm
Dimensions weighing platform (W×D×H)	320×260×60 mm
Material housing	plastic
Material weighing plate	stainless steel
Material display housing	Plastics

Functions

Underfloor weighing	None
IP protection - complete device	-
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Auto-off interval(s) in mains power mode	selectable
Tare function	manual (multi)
Number of keys for operation	2

Power Supply

Supplied power supply	Battery
Plug-in power supply type	Power adapter
	EURO
Plug-in power supply / adapter for countries - optional	UK US CH
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	9 V, 300 mA
Battery / accumulator type	Alkali(-Manganese)
Battery	6×1.5 V AA
Battery connection	Pad + Spring
Battery operating time	100 h
Battery voltage	9 V
Rechargeable battery	PCB-A01
Rechargeable battery operating time - backlight on	30 h
Rechargeable battery operating time - backlight off	30 h
Rechargeable battery charging time	10 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C

KERN ECB 10K-3N



Plain, mobile, uncomplicated

Storage temperature [Max] 60 °C

Approval

CE mark ✓

Services (optional)

Article number for adjustment at the location of installation 961-248

Article number for DAkkS calibration 963-128

Article number for certificate of conformity (verification) 969-517

Packing & Shipping

Delivery time 1 d

Dimensions packaging (W×D×H) 380×405×90 mm

Shipping method Parcel service

Net weight approx. 2,6 kg

Gross weight approx. 3,0 kg

Shipping weight 2,88 kg

Pictograms

STANDARD



OPTION

