

KERN EOC 100K-2XXL

Robust and high-resolution platform scale with practical Flip/Flop display device for greatest ease of use



Display type	LCD
Display backlight	✓
Display screen size	110×35 mm
Display segments	6
Display digit height - smallest digit	25 mm
Display digit height	25 mm

Construction

Dimension display device (W×D×H)	268×115×80 mm
Dimensions weighing surface (W×D)	950×500 mm
Dimensions weighing surface	950×500 mm
Dimensions weighing platform (W×D×H)	950×500×60 mm
Material weighing plate	stainless steel
Material platform	mild steel
Material display housing	Plastics
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand height	330 mm
Stand inclinable	✓
Wall mount	✓
Display device cable length	2,7 m
Load cells - number	4

Functions

Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	15.000
Smallest piece weight when piece counting - laboratory conditions	10 g
Smallest piece weight when piece counting - normal conditions	100 g
Reference quantity	10, 20, 50, 100, 200
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	IP65
IP protection - load cell	IP65

Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	EOC

Measuring System

Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	60 kg; 150 kg
Readability [d]	0,02 kg; 0,05 kg
Reproducibility	0,02 kg; 0,05 kg
Linearity	± 0,06 kg; 0,15 kg
Resolution	3.000, 3.000
Tare range	150 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Stabilization time	2 s
Warm-up time	10 min
Linearisation in dots	3
Eccentric loading at 1/3 [Max]	0,1 kg; 0,25 kg
Maximum creep (15 minutes)	200 g
Maximum creep (30 minutes)	400 g
Default unit	kg
Units	kg g lb oz PCS
Load cell connection	4-wire

Display

Display type	LCD
--------------	-----

KERN EOC 100K-2XXL

Robust and high-resolution platform scale with practical Flip/Flop display device for greatest ease of use

Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 30 min 15 min
Auto-off interval(s) in mains power mode	3 min off 5 min 30 min 15 min
Tare function	manual (single & multi)
Number of keys for operation	7

Interface	
Interfaces	RS-232 standard

Power Supply	
Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter

Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
---	------------------

Input voltage power supply / power [Max]	100 V-240 V, 0.4 A
--	--------------------

Input voltage device / power [Max]	12 V, 1000 mA
------------------------------------	---------------

Battery / accumulator type	Pb
----------------------------	----

Battery operating time	100 h
------------------------	-------

Rechargeable battery	6 V; 1.3 Ah
----------------------	-------------

Rechargeable battery operating time - backlight on	26 h
--	------

Rechargeable battery operating time - backlight off	43 h
---	------

Rechargeable battery charging time	3 h
------------------------------------	-----

Rechargeable battery optional	Rchrg. battery optional - intern
-------------------------------	----------------------------------

Environmental conditions	
--------------------------	--

Ambient temperature [Min]	-10 °C
---------------------------	--------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Min]	0 %
-------------------------------	-----

Humidity of environment [Max]	80 %
-------------------------------	------

Approval	
----------	--

CE mark	✓
---------	---

Services (optional)	
---------------------	--

Article number for adjustment at the location of installation	961-249
---	---------

Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

Packing & Shipping	
--------------------	--

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	1015×582×185 mm
------------------------------	-----------------

Net weight	16,2 kg
------------	---------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	17 kg
--------------------	-------

Gross weight approx.	20 kg
----------------------	-------

Shipping weight	21,9 kg
-----------------	---------

Pictograms	
------------	--

STANDARD



OPTION

