


KERN EOC 20K-3A

Robust and high-resolution platform scale with practical Flip/Flop display device for greatest ease of use



Display

Display type	LCD
Display type	LCD
Display backlight	✓
Display screen size	110×35 mm
Display segments	6
Display digit height - smallest digit	25 mm
Display digit height	25 mm

Construction

Dimension display device (W×D×H)	268×115×80 mm
Dimensions weighing surface (W×D)	300×300 mm
Dimensions weighing surface	300×300 mm
Dimensions weighing platform (W×D×H)	300×300×110 mm
Material weighing plate	stainless steel
Material platform	mild steel
Material display housing	plastic
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand height	330 mm
Stand inclinable	✓
Wall mount	✓
Display device cable length	3 m
Load cells - number	1

Functions

Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	12.000
Smallest piece weight when piece counting - laboratory conditions	2 g
Smallest piece weight when piece counting - normal conditions	20 g
Reference quantity	10, 20, 50, 100, 200
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	IP65

Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	EOC

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	24 kg
Readability [d]	0,002 kg
Reproducibility	0,002 kg
Linearity	± 0,006 kg
Resolution	12.000
Tare range	24 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	24 kg (M1)
Stabilization time	3 s
Linearisation in dots	3
Eccentric loading at 1/3 [Max]	0,01 kg
Construction type of the scale	Single-range balance
	kg
	g
Units	lb
	oz
	PCS
Load cell connection	4-wire
Maximum creep (15 minutes)	8 g
Maximum creep (30 minutes)	16 g
Default unit	kg
Loadcell type	aluminium IP65 silicone-coated

KERN EOC 20K-3A



Robust and high-resolution platform scale with practical Flip/Flop display device for greatest ease of use

IP protection - load cell	IP65
	3 min
	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	30 min
	15 min
	3 min
	off
Auto-off interval(s) in mains power mode	5 min
	30 min
	15 min
Tare function	manual (single & multi)
Number of keys for operation	7

Interface	
Interfaces	RS-232 standard

Power Supply	
Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH

Input voltage power supply / power [Max]	100 V-240 V, 0.4 A
Input voltage device / power [Max]	12 V, 1000 mA

Power socket for mains adapter	Inside plus, outside minus
--------------------------------	----------------------------

Battery / accumulator type	Pb
----------------------------	----

Battery operating time	100 h
------------------------	-------

Rechargeable battery	6 V; 1.3 Ah
----------------------	-------------

Rechargeable battery operating time - backlight on	26 h
--	------

Rechargeable battery operating time - backlight off	43 h
---	------

Rechargeable battery charging time	3 h
------------------------------------	-----

Rechargeable battery optional	Rchrg. battery optional - intern
-------------------------------	----------------------------------

Battery/Accu connected	fixed electrical connection, not insulated
------------------------	--

Environmental conditions

Ambient temperature [Min]	-10 °C
---------------------------	--------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Min]	0 %
-------------------------------	-----

Humidity of environment [Max]	80 %
-------------------------------	------

Approval	
CE mark	✓


Services (optional)	
Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	715×360×185 mm
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	8 kg
Shipping weight	9,5 kg
Shipping volume weight	9,5 kg

Product information	
GTIN/EAN number	4045761198203
Trade number	84238129
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

