



Discover more details and matching accessories online!

## All-round bench scale, protected by stainless steel and IP65 rating, verification optional

### Features

- **1** Ideal for the ever-increasing hygienic requirements in the food, pharmaceutical and chemical industries
- Your support in a HACCP-compliant quality system
- **2** Ideal for the robust industrial applications
- **3** Protection against dust and water splashes IP65 (only when using rechargeable battery pack)
- Thanks to rechargeable battery operation, compact, lightweight construction, it is suitable for the use in several locations (kitchens, sales offices, cafeterias, food industry laboratories, etc.)

- Thanks to the stainless steel design of the housing and platform with smooth surface, the scale is rust-free and easy to clean
- Recessed grips on the underside of the scale for easy transportation

### Technical data

- Large backlit LCD display, digit height 25 mm
- Dimensions weighing surface, stainless steel, W×D 233×193 mm
- Overall dimensions W×D×H 243×300×127 mm
- Rechargeable battery pack integrated, as standard, operating time up to 50 h without backlight, charging time approx. 12 h
- Net weight approx. 4,0 kg
- Permissible ambient temperature -10 °C/40 °C

#### STANDARD



#### OPTION



#### FACTORY



Model	Weighing capacity [Max] kg	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Options	
					Verification M III KERN	Calibr. Certificate DAkKS accr. KERN
<b>KERN</b>						
<b>FFN 1K-4N</b>	1,5	0,2	-	-	-	963-127
<b>FFN 3K0.5IPN</b>	3	0,5	-	-	-	963-127
<b>FFN 6K1IPN</b>	6	1	-	-	-	963-128
<b>FFN 15K2IPN</b>	15	2	-	-	-	963-128
<b>FFN 25K5IPN</b>	25	5	-	-	-	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.

<b>FFN 1K-4NM</b>	1,5	0,5	0,5	10	965-227	963-127
<b>FFN 3K1IPM</b>	3	1	1	20	965-227	963-127
<b>FFN 6K2IPM</b>	6	2	2	40	965-228	963-128
<b>FFN 15K5IPM</b>	15	5	5	100	965-228	963-128
<b>FFN 25K10IPM</b>	25	10	10	200	965-228	963-128