

# SAUTER FL 200

Universal digital force gauge with graphic-assisted display and integrated load cell



Material housing	metal, lacquered
Material display housing	Aluminium
Mounting - force application	External thread M6
Load support (tensile force)	Hook

## Functions

Limit-setting function	✓
Analogue signal	✓
Hold function	✓
Peak function	✓
Memory function	✓

## Interface

Interfaces	RS-232 standard USB-Device analogue (0 +/-2V)
------------	---

## Power Supply

Supplied power supply	Accu & Power supply
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO CH

Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
---	-------------------------------

Input voltage power supply / power [Max]	100 V - 240 V
--	---------------

Input voltage device / power [Max]	9 V, 500 mA
------------------------------------	-------------

Battery / accumulator type	NiMH
----------------------------	------

Battery capacity	750 mAh
------------------	---------

Battery voltage	4,8 V
-----------------	-------

Rechargeable battery	4,8 V 750 mA
----------------------	--------------

Rechargeable battery operating time - backlight on	8 h
--	-----

Rechargeable battery operating time - backlight off	10 h
---	------

Rechargeable battery charging time	8 h
------------------------------------	-----

## Environmental conditions

Ambient temperature [Min]	15 °C
---------------------------	-------

Ambient temperature [Max]	35 °C
---------------------------	-------

Storage temperature [Min]	-10 °C
---------------------------	--------

Storage temperature [Max]	40 °C
---------------------------	-------

## Category

Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge
Product family	FL-S

## Measuring System

Measuring range force [Max] (N)	250 N
Readability force [d] (N)	0,1 N
Measuring head measuring frequency	1000 Hz
Overload protection (% of [Max])	120%
Default unit	N
Internal data memory: Number of individual values	500
Internal data memory: Number of value groups	1
Number of platforms / channels	1
Tolerance (% of [Max])	0,2%
Directions of force	tension compression

## Display

Display type	LCD
Display digit height	8,5 mm
Screen reversible	✓

## Construction

Dimension housing (W×D×H)	175×75×30 mm
Dimensions completely mounted (W×D×H)	175×75×30 mm
Dimension display device (W×D×H)	175×75×30 mm

# SAUTER FL 200



Universal digital force gauge with graphic-assisted display and integrated load cell

## Approval

CE mark ✓

## Services (optional)

Article number for DAkkS calibration (tensile force) 963-161

Article number for DAkkS calibration (compressive force) 963-261

Article number for DAkkS calibration (tensile force/ compressive force) 963-361

Article number for factory calibration (tensile force) 961-161

Article number for factory calibration (compressive force) 961-261

Article number for factory calibration (tensile force/ compressive force) 961-361

## Packing & Shipping

Delivery time 1 d

Dimensions packaging (W×D×H) 260×230×75 mm

Shipping method Parcel service

Net weight approx. 0,55 kg

Gross weight approx. 1,4 kg

Shipping weight 1,386 kg

## Pictograms

### STANDARD



### OPTION

