

SAUTER FL 5K

Powerful digital force gauge with graphic assisted display for tensile and compressive force measurements with external load cell



Material housing	metal, lacquered
Material display housing	Aluminium
Mounting - force dissipation	Threaded hole M12
Mounting - force application	Threaded hole M12
Load support (tensile force)	Rod end

Functions	
Limit-setting function	✓
Analogue signal	✓
Memory function	✓

Interface	
Interfaces	RS-232 standard USB-Device analogue (0 +/-2V)

Power Supply	
Supplied power supply	Accu & Power supply
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	CH
Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US CH

Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	9 V, 500 mA
Battery / accumulator type	NiMH
Battery capacity	750 mAh
Battery voltage	4,8 V
Rechargeable battery	4,8 V 750 mA
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	10 h
Rechargeable battery charging time	8 h

Environmental conditions	
Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Category

Brand	Sauter
Product category	Force measurement
Product group	Digital force gauges (external measuring cell)
Product family	FL-M

Measuring System

Measuring range force [Max] (N)	5 kN
Readability force [d] (N)	2 N
Measuring head measuring frequency	1000 Hz
Overload protection (% of [Max])	120%
Default unit	N
Internal data memory: Number of individual values	500
Internal data memory: Number of value groups	1
Number of platforms / channels	1
Tolerance (% of [Max])	0,2%
Directions of force	tension compression

Display

Display type	LCD
Display digit height	8,5 mm
Screen reversible	✓

Construction

Dimension housing (W×D×H)	175×75×30 mm
Dimensions completely mounted (W×D×H)	175×75×30 mm
Dimension display device (W×D×H)	175×75×30 mm
Dimensions load cell	69,2×59,5×23,7 mm

SAUTER FL 5K



Powerful digital force gauge with graphic assisted display for tensile and compressive force measurements with external load cell

Approval

CE mark ✓

Services (optional)

Article number for DAkkS calibration (tensile force) 963-163

Article number for DAkkS calibration (compressive force) 963-263

Article number for DAkkS calibration (tensile force/ compressive force) 963-363

Article number for factory calibration (tensile force) 961-163

Article number for factory calibration (compressive force) 961-263

Article number for factory calibration (tensile force/ compressive force) 961-363

Packing & Shipping

Delivery time 1 d
Dimensions packaging (W×D×H) 370×325×115 mm
Shipping method Parcel service
Net weight approx. 1,4 kg
Gross weight approx. 2,4 kg
Shipping weight 2,8 kg

Pictograms

STANDARD



OPTION

