

KERN FS 2-1KOY2

Pre-configured set consisting of the premium force gauge FS-2 and the measuring cell CO 100-Y2 (For tensile force and compressive force measurements)



Functions

IP protection - load cell	IP65
Peak function	✓
Memory function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable

Interface

Interfaces	USB-Device
------------	------------

Power Supply

Supplied power supply	Accu & Power supply
Plug-in power supply type	USB including power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	UK
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	5 V, 1 A
Battery / accumulator type	Li-Ion
Battery connection	2-pole tub connector
Battery capacity	2.400 mAh
Battery voltage	3,7 V
Rechargeable battery	3,7V, 2400mAh
Rechargeable battery operating time - backlight on	5 h
Rechargeable battery operating time - backlight off	8 h
Rechargeable battery charging time	8 h

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration (tensile force)	963-162
Article number for DAkkS calibration (compressive force)	963-262
Article number for DAkkS calibration (tensile force/compressive force)	963-362

Category

Brand	Sauter
Product category	Force measurement
Product group	Force measuring device set
Product family	FS OY2

Measuring System

Measuring range force [Max] (N)	1 kN
Readability force [d] (N)	0,2 N
Measuring head measuring frequency	1000 Hz
Default unit	N
Number of platforms / channels	2
Directions of force	tension compression

Display

Display type	TFT, color
Display resolution	320×480
Languages of the user interface	German English French Spanish Italian

Construction

Dimensions load cell (cylindrical)	51×70 mm
Material housing	plastic
Material display housing	Plastics
Mounting - force dissipation	External thread M12
Mounting - force application	External thread M12

KERN FS 2-1KOY2




Pre-configured set consisting of the premium force gauge FS-2 and the measuring cell CO 100-Y2 (For tensile force and compressive force measurements)

Packing & Shipping

Delivery time	3 d
Net weight	0,755 kg
Shipping method	Parcel service
Net weight approx.	0,80 kg
Gross weight approx.	1,8 kg
Shipping weight	1,643 kg

Pictograms

STANDARD



OPTION

