

# SAUTER FS 2-1KSP1

Ready-assembled set consisting of premium force gauge FS 2 and external "S" measuring cell CS 100-3P1 for tensile and compressive force measurements



## Functions

IP protection - load cell	IP67
Peak function	✓
Memory function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable

## Interface

Interfaces	USB-Device
------------	------------

## Power Supply

Supplied power supply	Accu & Power supply
Plug-in power supply type	USB including power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	UK
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	5 V, 1 A
Battery / accumulator type	Li-Ion
Battery connection	2-pole tub connector
Battery capacity	2.400 mAh
Battery voltage	3,7 V
Rechargeable battery	3,7V, 2400mAh
Rechargeable battery operating time - backlight on	5 h
Rechargeable battery operating time - backlight off	8 h
Rechargeable battery charging time	8 h

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for DAkKS calibration (tensile force)	963-162
Article number for DAkKS calibration (compressive force)	963-262
Article number for DAkKS calibration (tensile force/compressive force)	963-362

## Category

Brand	Sauter
Product category	Force measurement
Product group	Force measuring device set
Product family	FS SP1

## Measuring System

Measuring range force [Max] (N)	1 kN
Readability force [d] (N)	0,2 N
Measuring head measuring frequency	1000 Hz
Default unit	N
Number of platforms / channels	2
Directions of force	tension compression

## Display

Display type	TFT, color
Display resolution	320×480
Languages of the user interface	German English French Spanish Italian

## Construction

Dimensions load cell	50,8×76,2×19 mm
Material housing	plastic
Material display housing	Plastics
Mounting - force dissipation	Threaded hole M10
Mounting - force application	Threaded hole M10

# SAUTER FS 2-1KSP1




Ready-assembled set consisting of premium force gauge FS 2 and external "S" measuring cell CS 100-3P1 for tensile and compressive force measurements

## Packing & Shipping

Delivery time	3 d
Shipping method	Parcel service
Net weight approx.	0,90 kg
Gross weight approx.	2,0 kg
Shipping weight	1,835 kg

## Pictograms

### STANDARD



### OPTION

