

KERN FXN 6K-3N

KERN

Bench scale, protected by stainless steel and protection type IP68



Category

Brand	KERN
Product category	Industrial scale
Product group	IP protected bench scale
Product family	FXN

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	6 kg
Readability [d]	0,001 kg
Reproducibility	0,001 kg
Linearity	± 0,002 kg
Resolution	6.000
Tare range	-6 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6 kg (M1)
Possible calibration points	6 kg
Stabilization time	2 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,003 kg
Maximum creep (15 minutes)	4 g
Maximum creep (30 minutes)	8 g
Default unit	kg
Units	kg g lb PCS
Loadcell type	628HZ-0.4

Display

Display type	LCD
Display backlight	✓
Display segments	6
Display digit height	25 mm

Construction

Dimension housing (W×D×H)	240×280×120 mm
Dimensions completely mounted (W×D×H)	240×280×120 mm
Dimensions weighing surface (W×D)	236×195 mm
Dimensions weighing surface	236×195 mm
Material housing	stainless steel, plastic
Material weighing plate	stainless steel
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Load cells - number	1

Functions

Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	None
Counting function	✓
Counting resolution (laboratory conditions)	6.000
Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Reference quantity	10, 20, 50, 100, 200
IP protection - complete device	IP68
	3 min
	6 min
	8 min
	off
Auto-off interval(s) in battery mode/rechargeable battery mode	4 min
	5 min
	2 min
	1 min
	7 min
	9 min
Tare function	manual (multi)
Number of keys for operation	5

Power Supply

Supplied power supply	Battery
-----------------------	---------

KERN FXN 6K-3N

Bench scale, protected by stainless steel and protection type IP68

Battery / accumulator type	Alkali(-Manganese)
Battery	4×1.5 V Size D
Battery connection	Battery insert
Battery operating time - backlight on	200 h
Battery operating time - backlight off	400 h
Battery operating time	200 h
Battery voltage	6 V

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	25 %
Humidity of environment [Max]	95 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	325×365×225 mm
Shipping method	Parcel service
Net weight approx.	3,2 kg
Gross weight approx.	3,8 kg
Shipping weight	5,3 kg

Pictograms

STANDARD



OPTION

