

KERN HCB 0.5T-3

Handy hanging scale for higher loads



Display

Display type	LCD
Display backlight	no
Display digit height	12 mm
Languages of the user interface	English
	Symbol language

Construction

Dimension housing (W×D×H)	82×43×153 mm
Dimensions housing - width (A)	82 mm
Dimensions housing - depth (B)	43 mm
Dimensions - total height/total length (D)	153 mm
Dimensions - inner length (E)	117 mm
Dimensions loop/top - hole diameter (F)	16 mm
Dimensions hook/bottom - hole diameter (G)	16 mm
Dimensions loop/top - thickness (H)	4 mm
Dimensions hook/bottom - thickness (I)	4 mm
Material housing	plastic
Material display housing	Plastics
Material load cell(s)	aluminium
Load cells - number	1

Functions

Function for averaging under unstable weighing conditions	✓
Hold function	✓
IP protection - load cell	no IP protection
Peak function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	off 4 min
Tare function	manual (multi)
Number of keys for operation	3

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	3×1.5 V AA
Battery connection	Pad + Spring
Battery operating time	300 h
Battery voltage	4,5 V

Category

Brand	KERN
Product category	Industrial scale
Product group	Hanging scale
Product family	HCB

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	500 kg
Readability [d]	1 kg
Reproducibility	1 kg
Linearity	± 2 kg
Resolution	500
Adjustment options	Adjusting with external weight
Recommended adjusting weight	200 kg (M3)
Possible calibration points	200 kg
Stabilization time	2 s
Warm-up time	10 min
Maximum creep (15 minutes)	2 kg
Maximum creep (30 minutes)	4 kg
Eccentric/Off-centre loading is not possible	✓
Default unit	kg
Units	kg lb N
Internal measuring frequency	5 Hz
Tolerance (% of [Max])	0,5%
Loadcell type	aluminium
Load cell connection	4-wire

KERN HCB 0.5T-3



Handy hanging scale for higher loads

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Max]	60 °C

Approval

CE mark	✓
TÜV-tested	✓

Services (optional)

Article number for adjustment at the location of installation	961-250
Article number for DAkkS calibration	963-130H
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	215×150×85 mm
Shipping method	Parcel service
Net weight approx.	0,40 kg
Gross weight approx.	0,70 kg
Shipping weight	0,68 kg

Pictograms

STANDARD



OPTION

