

KERN HFM 5T0.5

Robust industrial crane scale with bright LED display for optimum reading in unfavourable ambient conditions



Category

Brand	KERN
Product category	Industrial scale
Product group	Crane scale
Product family	HFM

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	5000 kg
Readability [d]	0,5 kg
Resolution	10.000
Linearity	± 5 kg
Reproducibility	2,5 kg
Tare range	-5000 kg
Default unit	kg
Units	kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	5000 kg (M1)
Possible calibration points	5000 kg
Stabilization time	2 s
Warm-up time	30 min
Eccentric/Off-centre loading is not possible	✓
Maximum creep (15 minutes)	2 kg
Maximum creep (30 minutes)	4 kg
Loadcell type	aluminium IP67 silicone-coated + glued on plate
Tolerance (% of [Max])	0,2%

Zulassung

CE mark	✓
---------	---

Display

Display type	LED segments
Display backlight	LED
Display digit height	30 mm
Languages of the user interface	English

Construction

Dimension display device (W×D×H)	300×190×230 mm
Dimensions housing - width (A)	300 mm
Dimensions housing - depth (B)	230 mm
Dimensions housing - height/length (C)	190 mm
Dimensions - total height/total length (D)	730 mm
Dimensions hook/bottom - hole diameter (G)	55 mm
Dimensions - inner length (E)	650 mm
Dimensions loop/top - hole diameter (F)	74 mm
Dimensions completely mounted (W×D×H)	310×230×800 mm
Material display housing	Cast aluminium
Material housing	cast aluminium
Material load hook	steel, varnished
Material load cell(s)	aluminium

Functions

Number of keys for operation	4
	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 10 min 30 min 20 min
Wireless operation	✓
Tare function	manual (multi)
Hold function	✓
Range of radio module	20 m
Underfloor weighing	None
IP protection - load cell	IP67

Power Supply

Input voltage power supply / power [Max]	110 V - 230 V AC
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter

KERN HFM 5T0.5

KERN

Robust industrial crane scale with bright LED display for optimum reading in unfavourable ambient conditions

Supplied power supply	Accu & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery charging time	14 h
Rechargeable battery operating time - backlight on	50 h
Rechargeable battery operating time - backlight off	50 h
Battery	1×12 V, Type 23 A
Battery / accumulator type	Pb
Battery connection	Plug-in terminals
Battery capacity	10.000 mAh
Battery voltage	6 V
Battery operating time	50 h

Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	400×810×455 mm
Net weight	17,8 kg
Shipping method	Parcel service
Net weight approx.	18 kg
Gross weight approx.	28 kg
Shipping weight	29,5 kg

Services (optional)

Article number for adjustment at the location of installation	961-252
Article number for DAkkS calibration	963-132H
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

