

KERN HFM 5T0.5

Robust industrial crane scale with bright LED display for optimum reading in unfavourable ambient conditions



Construction

Dimensions completely mounted (W×D×H)	310×230×800 mm
Dimension display device (W×D×H)	300×190×230 mm
Dimensions housing - width (A)	300 mm
Dimensions housing - depth (B)	230 mm
Dimensions housing - height/length (C)	190 mm
Dimensions - total height/total length (D)	730 mm
Dimensions - inner length (E)	650 mm
Dimensions loop/top - hole diameter (F)	74 mm
Dimensions hook/bottom - hole diameter (G)	55 mm
Material housing	cast aluminium
Material load hook	steel, lacquered
Material display housing	cast aluminium
Material load cell(s)	stainless steel
Load cells - number	1

Functions

Wireless operation	✓
Underfloor weighing	None
Range of radio module	20 m
Hold function	✓
	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 10 min 30 min 20 min
Tare function	manual (multi)
Number of keys for operation	4

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	110 V - 230 V AC
Input voltage device / power [Max]	12 V, 500 mA

Category

Brand	KERN
Product category	Industrial scale
Product group	Crane scale
Product family	HFM

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	5000 kg
Readability [d]	0,5 kg
Reproducibility	2,5 kg
Linearity	± 5 kg
Resolution	10.000
Tare range	-5000 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	5000 kg (M1)
Eccentric/Off-centre loading is not possible	✓
Stabilization time	2 s
Construction type of the scale	Single-range balance
Units	kg
Tolerance (% of [Max])	0,2%
Maximum creep (15 minutes)	2 kg
Maximum creep (30 minutes)	4 kg
Default unit	kg

Display

Display type	LED segments
Display backlight	LED
Display digit height	30 mm
Languages of the user interface	English

KERN HFM 5T0.5



Robust industrial crane scale with bright LED display for optimum reading in unfavourable ambient conditions

Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
Battery / accumulator type	Pb
Battery	1×12 V, Type 23 A
Battery connection	Plug-in terminals
Battery operating time	50 h
Battery capacity	10.000 mAh
Battery voltage	6 V
Battery - Number of cells	1
Battery - Individual weight	1570 g
Battery - Total weight	1570 g
Battery - Construction	Individual cells
Battery capacity (Wh)	60 Wh
Battery - Tests passed UN 38.3	✓
Rechargeable battery	6 V, 10 Ah
Rechargeable battery operating time - backlight on	50 h
Rechargeable battery operating time - backlight off	50 h
Rechargeable battery charging time	14 h
Battery/Accu connected	fixed electrical connection, no leakage current (insulated)

Environmental conditions	
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval	
CE mark	✓
TÜV-tested	✓


Services (optional)	
Article number for adjustment at the location of installation	961-252
Article number for DAkkS calibration	963-132H
Article number for certificate of conformity	969-517

Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	400×810×455 mm
Shipping method	Parcel service
Net weight approx.	18 kg
Gross weight approx.	28 kg
Shipping weight	29,5 kg
Shipping volume weight	29,5 kg

Product information	
GTIN/EAN number	4045761111707
Trade number	84238220
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

