

KERN IFS 100K-2LM

Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution 60.000 points, verification optional



Display digit height - smallest digit	13,5 mm
Display digit height	16,5 mm

Construction

Dimensions completely mounted (W×D×H)	650×500×140 mm
Dimension display device (W×D×H)	260×150×65 mm
Dimensions weighing surface (W×D)	650×500 mm
Dimensions weighing surface	650×500 mm
Dimensions weighing platform (W×D×H)	650×500×140 mm
Material weighing plate	stainless steel
Material platform	mild steel
Material display housing	Plastics
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand height	330 mm
Stand inclinable	✓
Wall mount	✓
Cable length	2,5 m
Display device cable length	3 m
Load cells - number	1

Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
PLU - total	100
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Counting function	✓
Counting resolution (laboratory conditions)	60.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	2,5 g
Smallest piece weight when piece counting - normal conditions	25 g
Reference quantity	n (any number of pieces)
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	no IP protection
IP protection - load cell	IP65
Peak function	✓

Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	IFS

Measuring System

Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	60 kg; 150 kg
Readability [d]	0,02 kg; 0,05 kg
Reproducibility	0,02 kg; 0,05 kg
Linearity	± 0,02 kg; 0,05 kg
Minimum weight [Min]	0,4 kg; 1 kg
Resolution	3.000, 3.000
Tare range	150 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Stabilization time	2 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	0,02 kg; 0,05 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	6-wire

Display

Display type	LCD
Display backlight	✓

KERN IFS 100K-2LM

Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution 60.000 points, verification optional

Memory function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	21

Interface	
Interfaces	RS-232 standard

Power Supply	
Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH

Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US
	CH

Input voltage power supply / power [Max]	100 - 240 V~ 50/60 Hz 190 mA
--	---------------------------------

Input voltage device / power [Max]	12 V, 500 mA
------------------------------------	--------------

Battery / accumulator type	Pb
----------------------------	----

Rechargeable battery	6 V, 1.2 Ah
----------------------	-------------

Rechargeable battery operating time - backlight on	8 h
--	-----

Rechargeable battery operating time - backlight off	18 h
---	------

Rechargeable battery charging time	12 h
------------------------------------	------

Rechargeable battery optional	Rchrg. battery optional (factory)
-------------------------------	-----------------------------------

Environmental conditions	
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval	
CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III

Verification scale interval [e]	0,02 kg; 0,05 kg
---------------------------------	------------------

Services (optional)	
Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129
Article number for certificate of conformity	969-517

Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	1045×660×240 mm
Shipping method	Parcel service
Net weight approx.	22 kg
Gross weight approx.	26 kg
Shipping weight	33,1 kg

Pictograms

STANDARD



OPTION



FACTORY

