

KERN IFS 300K-3

Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution 60.000 points



Construction

Dimensions completely mounted (W×D×H)	650×500×745 mm
Dimension display device (W×D×H)	260×150×65 mm
Dimensions weighing surface (W×D)	650×500 mm
Dimensions weighing surface	650×500 mm
Dimensions weighing platform (W×D×H)	650×500×140 mm
Material weighing plate	stainless steel
Material platform	mild steel
Material display housing	plastic
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand height	600 mm
Stand inclinable	✓
Wall mount	✓
Display device cable length	3 m
Load cells - number	1

Functions

Sum memory function	✓
Recipe/summing level	Sum A
PLU - total	100
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Counting function	✓
Counting resolution (laboratory conditions)	60.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	5 g
Smallest piece weight when piece counting - normal conditions	50 g
Reference quantity	n (any number of pieces)
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	no IP protection
IP protection - load cell	IP65
Peak function	✓
Memory function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off
Auto-off interval(s) in mains power mode	selectable

Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	IFS

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	150 kg; 300 kg
Readability [d]	0,002 kg; 0,005 kg
Reproducibility	0,002 kg; 0,005 kg
Linearity	± 0,014 kg; 0,03 kg
Resolution	75.000, 60.000
Tare range	300 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	300 kg (F2)
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,05 kg
Construction type of the scale	Multi-division balance
Units	kg
Load cell connection	6-wire
Maximum creep (15 minutes)	50 g
Maximum creep (30 minutes)	100 g
Default unit	kg
Loadcell type	aluminium IP65 silicone-coated

Display

Display type	LCD
Display backlight	✓
Display digit height - smallest digit	13,5 mm
Display digit height	16,5 mm

KERN IFS 300K-3



Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution 60.000 points

Tare function	manual (multi)
Number of keys for operation	21

Interface	
Interfaces	RS-232 standard

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH

Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US
	CH

Power supply - Cable length	180 cm
-----------------------------	--------

Input voltage power supply / power [Max]	100 - 240 V~ 50/60 Hz 190 mA
--	---------------------------------

Power supply cable removable	removable
------------------------------	-----------

Input voltage device / power [Max]	12 V, 500 mA
------------------------------------	--------------

Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
--------------------------------	--

Battery / accumulator type	Pb
----------------------------	----

Rechargeable battery	6 V, 1.2 Ah
----------------------	-------------

Rechargeable battery operating time - backlight on	8 h
--	-----

Rechargeable battery operating time - backlight off	18 h
---	------

Rechargeable battery charging time	12 h
------------------------------------	------

Rechargeable battery optional	Rchrg. battery optional (factory)
-------------------------------	-----------------------------------

Environmental conditions

Ambient temperature [Min]	0 °C
---------------------------	------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Min]	0 %
-------------------------------	-----

Humidity of environment [Max]	80 %
-------------------------------	------

Storage temperature [Min]	-20 °C
---------------------------	--------

Storage temperature [Max]	60 °C
---------------------------	-------

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-129
--------------------------------------	---------

Article number for certificate of conformity	969-517
--	---------

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	1045×660×240 mm
------------------------------	-----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	22 kg
--------------------	-------

Gross weight approx.	26 kg
----------------------	-------

Shipping weight	33,1 kg
-----------------	---------

Shipping volume weight	33,1 kg
------------------------	---------

Product information

GTIN/EAN number	4045761144859
-----------------	---------------

Trade number	84238220
--------------	----------

REACH classification	no prohibited substances
----------------------	--------------------------

Pictograms

STANDARD



OPTION



FACTORY

