

KERN IFS 60K0.5DL

Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution 60.000 points



Construction

Dimensions completely mounted (W×D×H)	500×400×120 mm
Dimension display device (W×D×H)	260×150×65 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×120 mm
Material weighing plate	stainless steel
Material platform	mild steel
Material display housing	plastic
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand height	600 mm
Stand inclinable	✓
Wall mount	✓
Display device cable length	3 m
Load cells - number	1

Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	IFS

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	30 kg; 60 kg
Readability [d]	0,0005 kg; 0,001 kg
Reproducibility	0,0005 kg; 0,001 kg
Linearity	± 0,003 kg; 0,006 kg
Resolution	60.000, 60.000
Tare range	60 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	50 kg (F2)
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,004 kg; 0,008 kg
Construction type of the scale	Multi-division balance
Units	kg
Load cell connection	4-wire
Maximum creep (15 minutes)	10 g
Maximum creep (30 minutes)	20 g
Default unit	kg
Loadcell type	aluminium IP65 silicone-coated

Display

Display type	LCD
Display backlight	✓
Display digit height - smallest digit	13,5 mm
Display digit height	16,5 mm

Functions

Sum memory function	✓
Recipe/summing level	Sum A
PLU - total	100
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Counting function	✓
Counting resolution (laboratory conditions)	60.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Reference quantity	n (any number of pieces)
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	no IP protection
IP protection - load cell	IP65
Peak function	✓
Memory function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off
Auto-off interval(s) in mains power mode	off

KERN IFS 60K0.5DL

Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution 60.000 points

Tare function	manual (multi)
Number of keys for operation	21

Interface	
Interfaces	RS-232 standard

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH

Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US
	CH

Power supply - Cable length	180 cm
-----------------------------	--------

Input voltage power supply / power [Max]	100 - 240 V~ 50/60 Hz 190 mA
--	---------------------------------

Power supply cable removable	removable
------------------------------	-----------

Input voltage device / power [Max]	12 V, 500 mA
------------------------------------	--------------

Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
--------------------------------	--

Battery / accumulator type	Pb
----------------------------	----

Rechargeable battery	6 V, 1.2 Ah
----------------------	-------------

Rechargeable battery operating time - backlight on	8 h
--	-----

Rechargeable battery operating time - backlight off	18 h
---	------

Rechargeable battery charging time	12 h
------------------------------------	------

Rechargeable battery optional	Rchrg. battery optional (factory)
-------------------------------	-----------------------------------

Environmental conditions

Ambient temperature [Min]	0 °C
---------------------------	------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Min]	0 %
-------------------------------	-----

Humidity of environment [Max]	80 %
-------------------------------	------

Storage temperature [Min]	-20 °C
---------------------------	--------

Storage temperature [Max]	60 °C
---------------------------	-------

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-129
--------------------------------------	---------

Article number for certificate of conformity	969-517
--	---------

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	930×545×210 mm
------------------------------	----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	12 kg
--------------------	-------

Gross weight approx.	15 kg
----------------------	-------

Shipping weight	21,3 kg
-----------------	---------

Shipping volume weight	21,3 kg
------------------------	---------

Product information

GTIN/EAN number	4045761111936
-----------------	---------------

Trade number	84238220
--------------	----------

REACH classification	no prohibited substances
----------------------	--------------------------

Pictograms

STANDARD



OPTION



FACTORY

