

SAUTER LB 500-2

KERN

Distance measurement directly in machines or sites with RS-232 interface



Battery / accumulator type	Alkali(-Manganese)
Battery	3 V CR2032
Battery voltage	3 V

Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	650×35×50 mm
Shipping method	Parcel service
Net weight approx.	0,60 kg
Gross weight approx.	0,65 kg
Shipping weight	0,65 kg

Pictograms

STANDARD



OPTION



Category

Brand	Sauter
Product category	Length measurement
Product group	Digital Length Measuring Device
Product family	LB

Measuring System

Measuring range length [Max]	500 mm
Division	0,01 mm
Tolerance (% of [Max])	3%

Display

Display type	LCD
--------------	-----

Construction

Dimension housing (W×D×H)	77×43×34 mm
Dimensions completely mounted (W×D×H)	640×30×42 mm
Material housing	cast aluminium, plastic
Measurement alignment	vertical/horizontal

Functions

Length measuring - zero setting	✓
Pre-added and pre-reduced length manually adjustable	✓

Interface

Interfaces	RS-232 (optional)
------------	-------------------

Power Supply

Supplied power supply	Battery
-----------------------	---------