

# KERN OBN 135T24 1

The digital laboratory assistant with infinity optical unit and professional Koehler illumination



## Category

Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OBN-S

## Zulassung

CE mark	✓
---------	---

## Display

Display resolution	2048×1536
--------------------	-----------

## Construction

Dimension (W×D×H)	390×235×620 mm
Optical system	Infinity
Tube type	Siedentopf
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Lens quality	Infinity Plan
	4×
	10×
Standard objectives	20×
	40×
	100×
Nosepiece screw-in locations	5
Dioptr adjustment	both-sided
Dioptr adjustment [Min]	-5
Dioptr adjustment [Max]	5
Contrasting methods	Bright field Darkfield (optional) Polarisation (optional)

	Fluorescent (optional) Phase contrast (optional)
Light distribution	100:0
Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	50 mm
Camera - Adapter type	C-Mount
Supported camera types	Microscope Camera
Cameratype	Tablet camera
Camera - Sensor type	Sony CMOS
Camera - Sensor size	1/2,8"
Camera - Resolution	5 MP
C-Mount focusable	✓
C-Mount magnification	0,5 x
Camera - Colour depth	Colour
Camera - Framerate	30 fps
Camera- Mounting types	C-mount thread
Camera - Exposure method	Rolling Shutter

## Ocular

Ocular field width	HWF
Ocular magnifications	10 x
Ocular visual field	20 mm
Ocular diameter	23,2 mm

## Focussing

Fine drive minimum	0,002 mm
Torque regulation	✓
Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Focusing mechanism	coaxial coarse and fine drive

## Illumination

Illumination type incident light	none
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Field diaphragm	✓
Aperture diaphragm	✓
Koehler illumination	✓
Filter possible	✓

## Functions

Memory - total size	128 GB
Interfaces	WiFi standard USB 2.0

# KERN OBN 135T24 1



The digital laboratory assistant with infinity optical unit and professional Koehler illumination

	HDMI
	MicroSD card slot
Supported operating systems	Android
Camera - Applicable software	integrated

## Power Supply

Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	100 - 240 V
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Net weight	10,973 kg
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	14 kg
Shipping weight	20,2 kg

## Pictograms