

KERN OBS 105

KERN

The school microscope – for the first steps in microscopy and for use in biology lessons



Category

Brand	Optics
Product category	Microscope
Product group	Compound microscope
Product family	OBS-1

Construction

Dimension (W×D×H)	130×300×310 mm
Optical system	Finite
Tube type	Monocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Contrasting methods	Bright field
Standard objectives	4× 10× 40×
Lens quality	achromatic
Nosepiece screw-in locations	4
Eyepieces fixed	✓
Interpupillary distance [Min]	55 mm
Interpupillary distance [Max]	75 mm

Ocular

Ocular type	Eyepiece WF 10x / Ø 18mm with anti-fungus
Ocular field width	WF
Eye point	Standard
Ocular magnifications	10x
Ocular visual field	18 mm
Ocular diameter	23,2 mm

Objective

Objectives - Details	Objective Achromatic 10x / 0,25 anti-fungus Objective Achromatic 4x / 0,1 anti-fungus Objective Achromatic 40x / 0,65 spring, anti-fungus
Objectives magnifications	4x / 10x / 40x

Illumination

Illuminance	Transmitted light
Illumination type transmitted light	LED
Illumination intensity transmitted light	0,5 W
Illumination dimmable	Transmitted light
Filter possible	✓
Aperture diaphragm	✓

Focussing

Field of view [Min]	0,45 mm
Field of view [Max]	4,5 mm
Fine drive minimum	0,00025 mm
Focusing mechanism	coaxial coarse and fine drive

Condensor

Condensor type	Abbe
----------------	------

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO UK
Input voltage power supply / power [Max]	100 - 240 V
Power supply cable removable	removable
Input voltage device / power [Max]	6 V, 500 mA
Battery / accumulator type	NiMH
Battery	3×1.2V AA
Battery connection	Plug-in terminals
Rechargeable battery operating time - backlight on	4 h
Rechargeable battery charging time	10 h

KERN OBS 105

KERN

The school microscope – for the first steps in microscopy and for use in biology lessons

Battery/Accu connected	fixed electrical connection, not insulated
------------------------	--

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	425×280×220 mm
Shipping method	Parcel service
Net weight approx.	3,2 kg
Gross weight approx.	4,0 kg
Shipping weight	5,2 kg
Shipping volume weight	5,2 kg

Product information

GTIN/EAN number	4045761228382
Trade number	90118000
REACH classification	no prohibited substances

Pictograms

STANDARD

