

KERN ODC 825



Specialists in microscopy for measurement, counting, documentation, archiving and image processing



Category

Brand	Optics
Product category	Microscope
Product group	Microscope camera
Product family	ODC-82

Zulassung

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	80×80×45 mm
Material display housing	No display available
Cameratype	USB2 Microscope camera - C-Mount
Camera - Sensor type	Aptina CMOS
Camera - Sensor size	1/2,5"
Camera - Resolution	5,1 MP
Camera - Colour depth	Colour
Camera- Mounting types	C-mount
Camera - Exposure method	Rolling Shutter

Functions

Interfaces	USB 2.0
Supported operating systems	Win XP
	Win Vista
	Win 7
	Win 8
	Win 10
	Linux
Camera - Applicable software	OSx /Mac OS X)
	Win 11
Camera - Applicable software	external (OXM 902)

Power Supply

Input voltage device / power [Max]	5 V, 170 mA
------------------------------------	-------------

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	164×164×75 mm
Net weight	0,5829 kg
Shipping method	Parcel service
Net weight approx.	0,60 kg
Gross weight approx.	1,00 kg
Shipping weight	1 kg

Pictograms

STANDARD

