


KERN ODC 841



Specialists in microscopy for measurement, counting, documentation, archiving and image processing



Power Supply

Input voltage device / power [Max] 5 V, 435 mA

Environmental conditions

Storage temperature [Min] -5 °C

Storage temperature [Max] 40 °C

Packing & Shipping

Readability force [d] (N) 1 d

Dimensions packaging (W×D×H) 150×150×100 mm

Net weight 0,46 kg

Shipping method Parcel service

Net weight approx. 0,50 kg

Gross weight approx. 0,65 kg

Shipping weight 0,6245 kg

Pictograms

STANDARD



Category

Brand	Optics
Product category	Microscope
Product group	Microscope camera
Product family	ODC-84

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	68×68×46 mm
Cameratype	USB3 Microscope camera - C-Mount
Camera - Sensor type	Sony CMOS
Camera - Sensor size	1"
Camera - Resolution	20 MP
Camera - Colour depth	Colour
Camera- Mounting types	C-mount
Camera - Exposure method	Rolling Shutter

Functions

Interfaces	USB 3.0
Supported operating systems	Win XP Win Vista Win 7 Win 8 Win 10 Linux OSx /Mac OS X Win 11
Camera - Applicable software	external (OXM 902)