

KERN ORA 82BB

KERN

Refractive index measurement for laboratories and the industry



Storage temperature [Max] 40 °C

Packing & Shipping

Dimensions transport container (W×D×H)	205×75×55 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	215×94×65 mm
Net weight	0,24772 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,30 kg
Shipping weight	0,3 kg

Services (optional)

Article number for factory calibration	961-290
--	---------

Pictograms

STANDARD



Category

Brand	Optics
Product category	Refractometer
Product group	Analogue refractometer
Product family	ORA-B

Measuring System

Measuring method	Light refraction
Area of application	Sugar
Appropriate calibration liquid	78,8 % (clove oil)
Calibration block required	✓
Measurement temperature [Min] (°C)	10 °C
Measurement temperature [Max] (°C)	30 °C
Brix scale	✓
Readout Brix	0,5 %
Measuring range Brix [Min]	45 %
Measuring range Brix [Max]	82 %

Construction

Dimension (W×D×H)	137×40×40 mm
Refractometer type	Handheld refractometer
Scale - Display type	Analogue
Material prism	ZLaF3 lanthanum flint glass nd=1.85544

Functions

IP protection - complete device	-
---------------------------------	---

Environmental conditions

Storage temperature [Min]	-5 °C
---------------------------	-------