

# KERN ORM 1WN

# KERN

Digital measurement of refraction index for universal application



Measuring range KMW (Babo) [Min]	0 °KMW
Measuring range KMW (Babo) [Max]	25 °KMW
Readout KMW (Babo)	0,1 °KMW
Accuracy KMW (Babo)	±0,2 °KMW
Scale KMW (Babo)	✓
Measuring range Oechsle [Min]	0 °Oe
Measuring range Oechsle [Max]	150 °Oe
Readout Oechsle	1 °Oe
Accuracy Oechsle	±2 °Oe
Scale Oechsle	✓
Measuring range volume percentage [Min]	0 %
Measuring range volume percentage [Max]	22 %
Readout volume percentage	0,1 %
Accuracy volume percentage	±0,2 %
Appropriate calibration liquid	0 % (distilled water)
Measuring range Brix [Max]	50 %
Brix scale	✓
Area of application	Wine

<b>Construction</b>	
Dimension (W×D×H)	121×58×25 mm
Refractometer type	Handheld refractometer
Scale - Display type	Digital
Prism lid	✓
Material prism	ZLaF3 lanthanum flint glass nd=1.85544

<b>Functions</b>	
Averaging measurement	✓
Averaging measurement amount	15
IP protection - complete device	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	60 sec

<b>Power Supply</b>	
Supplied power supply	Battery
Power supply cable removable	removable
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	1.300 mAh
Battery voltage	1,5 V
Battery - Number of cells	1
Battery - Individual weight	11,5 g
Battery - Total weight	11,5 g

<b>Category</b>	
Brand	Optics
Product category	Refractometer
Product group	Digital refractometer
Product family	ORM-WN
<b>Measuring System</b>	
Measurement temperature [Min] (°C)	0 °C
Percentage by volume	0,0-22,0%(v/v) @ 0,1% (v/v) ± 0,2%(v/v)
Measurement temperature [Max] (°C)	40 °C
Precision	0,2 % 2 °Oe 0,2 °KMW 0,2 %(v/v)
Measuring method	Total reflection
Measuring range Brix [Min]	0 %
Scales	Brix Oechsle KMW (Babo) Volume percent
Measuring ranges	0,0 % - 50,0 % 0,0 °Oe - 150,0 °Oe 0,0 °KMW - 25,0 °KMW 0,0 %(v/v) - 22,0 %(v/v)
Readabilites [d]	0,1 % 1 °Oe 0,1 °KMW 0,1 %(v/v)
Readout Brix	0,1 %
Automatic temperature compensation (ATC)	✓
Accuracy Brix	±0,2 %
Scale volume percentage	✓

# KERN ORM 1WN



Digital measurement of refraction index for universal application

Battery - Construction	Individual cells
Battery capacity (Wh)	1,95 Wh
Battery - Lithium content	0 g
Battery/Accu connected	not connected, enclosed

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for factory calibration	961-290
--	---------

## Packing & Shipping

Dimensions transport container (W×D×H)	170×110×50 mm
Delivery time	1 d
Dimensions packaging (W×D×H)	170×110×50 mm
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,35 kg
Shipping weight	0,31 kg

## Product information

GTIN/EAN number	404576 1335585
Trade number	90275000
REACH classification	no prohibited substances

## Pictograms

### STANDARD

