

KERN OZP 558C825

KERN

First-class optics as well as strong illumination combined with a high level of flexibility and digital tools



Category

Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OZP-S

Construction

Dimension (W×D×H)	330×285×540 mm
Optical system	Greenough
Tube type	Trinocular
Tube angle of inclination	35°
Tube 360° rotation	✓
Light distribution	100:0
Contrasting methods	Bright field Darkfield (optional)
Interpupillary distance [Min]	52 mm
Interpupillary distance [Max]	76 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-6
Diopter adjustment [Max]	6

Functions

Camera - Applicable software	external (OXM 901, OXM 902)
Supported operating systems	Win XP Win Vista Win 7 Win 8 Win 10

Interface

Interfaces	USB 2.0
------------	---------

Ocular

Ocular field width	HSWF
Ocular magnifications	10 x
Ocular visual field	23 mm
Ocular diameter	30 mm

Objective

Objectives magnifications	0,6 x - 5,5 x
---------------------------	---------------

Illumination

Illuminance	Transmitted light
Illumination type incident light	LED
Illumination type transmitted light	LED
Illumination intensity incident light	3 W
Illumination intensity transmitted light	3 W
Illumination dimmable	Incident light + Transmitted light, separate

Focussing

Field of view [Min]	4,2 mm
Field of view [Max]	38,3 mm
Zoom [Min]	0,6 x
Zoom [Max]	5,5 x
Sample height [Max]	110 mm
Torque regulation	✓
Working distance	108 mm
Magnification ratio	9,2:1
Focusing mechanism	coarse drive

Stereomicroscope stand

Stand type	pillar
Diameter mounting microscope head (Ø)	76 mm

Camera

Cameratype	USB2 Microscope camera - C-Mount
Camera - Resolution	5,1 MP
Camera - Sensor type	CMOS
Camera - Sensor size	1/2,5"
Camera - Colour depth	Colour
Camera - Framerate	6,8 - 55 fps
Camera- Mounting types	C-mount thread
Camera - Exposure method	Rolling Shutter

KERN OZP 558C825



First-class optics as well as strong illumination combined with a high level of flexibility and digital tools

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH
Input voltage power supply / power [Max]	100 - 240 V AC, 50/60 Hz, 1,0 A
Input voltage device / power [Max]	12 V, 2000 mA

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	8 kg
Shipping weight	20,2 kg

Pictograms