

SAUTER SD 500N100

KERN

Manual test stand for tensile and compressive testing of springs, medium version up to 500 N



Category

Brand	Sauter
Product category	Test bench
Product group	Manual test stand
Product family	SD-M

Measuring System

Measuring range force [Max] (N)	500 N
Readability force [d] (N)	0,1 N
Measurable length [Max]	10 cm
Default unit	N
Units	kg N lbf
Internal data memory: Number of individual values	10
Internal data memory: Number of value groups	1
Tolerance (% of [Max])	0,5%

Display

Display type	LCD
Display digit height	10 mm

Construction

Dimension (W×D×H)	235×300×620 mm
Dimension housing (W×D×H)	235×300×620 mm
Dimensions completely mounted (W×D×H)	235×300×620 mm
Material housing	metal, lacquered
Type of drive	manual crank handle
Measuring room height [Max]	100 mm

Traverse distance with lever movement / release [Max]	100 mm
---	--------

Functions

Limit-setting function	✓
Length measuring - zero setting	✓
Hold function	✓
Peak function	✓
Statistic function	✓

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	UK CH
Input voltage power supply / power [Max]	220 V AC, 50 Hz
Input voltage device / power [Max]	230 V AC, 50 Hz

Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration	961-2610
--	----------

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	400×360×620 mm
Shipping method	Freight
Net weight approx.	22 kg
Gross weight approx.	30 kg
Shipping weight	29 kg

SAUTER SD 500N100



Manual test stand for tensile and compressive testing of springs, medium version up to 500 N

Pictograms

STANDARD



OPTION

