

# SAUTER TB 2000-0.1F

# KERN

Practical measuring device for measuring the thickness of layers for daily use



Dimensions completely mounted (W×D×H)	161×69×32 mm
---------------------------------------	--------------

Material housing	plastic
------------------	---------

Cable length	1 m
--------------	-----

## Functions

Increase in measurement accuracy possible	✓
---	---

## Power Supply

Supplied power supply	Battery
-----------------------	---------

Battery / accumulator type	Alkali(-Manganese)
----------------------------	--------------------

Battery	4×1.5 V AA
---------	------------

Battery capacity	2.600 mAh
------------------	-----------

Battery voltage	1,5 V
-----------------	-------

## Environmental conditions

Ambient temperature [Min]	-10 °C
---------------------------	--------

Ambient temperature [Max]	40 °C
---------------------------	-------

Storage temperature [Min]	-10 °C
---------------------------	--------

Storage temperature [Max]	40 °C
---------------------------	-------

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for factory calibration	961-110
--	---------

## Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	265×215×71 mm
------------------------------	---------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	0,30 kg
--------------------	---------

Gross weight approx.	0,75 kg
----------------------	---------

Shipping weight	0,8 kg
-----------------	--------

## Category

Brand	Sauter
-------	--------

Product category	Coating thickness measuring device
------------------	------------------------------------

Product group	Digital coating thickness gauge
---------------	---------------------------------

Product family	TB
----------------	----

## Measuring System

Offset accur (% of [Max])	1%
---------------------------	----

Measuring range coating thickness [d] (µm)	100 µm; 2000 µm
--	-----------------

Readability coating thickness [d] (µm)	0,1 µm; 1 µm
--	--------------

Coating thickness gauge sensor type	FE
-------------------------------------	----

Test object thickness coating	Non-magnetic coatings on iron, steel, Type F
-------------------------------	--

Minimum thickness base material	300 µm
---------------------------------	--------

Smallest sample, flat [radius]	6 mm
--------------------------------	------

Smallest sample, convex [radius]	1,5 mm
----------------------------------	--------

Smallest sample, concave [radius]	25 mm
-----------------------------------	-------

Sensor placement position	external
---------------------------	----------

Units	µm inch (mil)
-------	------------------

Tolerance (% of [Max])	3%
------------------------	----

## Display

Display type	LCD
--------------	-----

## Construction

Dimension (W×D×H)	161×69×32 mm
-------------------	--------------

Dimension housing (W×D×H)	161×69×32 mm
---------------------------	--------------

# SAUTER TB 2000-0.1F



Practical measuring device for measuring the thickness of layers for daily use

## Pictograms

### STANDARD

---



### OPTION

---

