

KERN TC 1250-0.1F

KERN

Robust coating thickness gauge – compact and easy to use



Dimension housing (W×D×H)	125×65×26 mm
Dimensions completely mounted (W×D×H)	125×65×26 mm
Material housing	plastic

Functions

Increase in measurement accuracy possible	✓
---	---

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	4×1.5 V AAA
Battery connection	Pad + Spring
Battery operating time	50 h
Battery capacity	1.100 mAh
Battery voltage	1,5 V

Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	50 °C
Storage temperature [Min]	0 °C
Storage temperature [Max]	50 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration	961-110
--	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	260×218×75 mm
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,75 kg
Shipping weight	0,9 kg

Category

Brand	Sauter
Product category	Coating thickness measuring device
Product group	Digital coating thickness gauge
Product family	TC

Measuring System

Offset accur (% of [Max])	1%
Measuring range coating thickness [d] (µm)	100 µm; 1250 µm
Readability coating thickness [d] (µm)	0,1 µm; 1 µm
Coating thickness gauge sensor type	FE
Test object thickness coating	Non-magnetic coatings on iron, steel, Type F
Minimum thickness coating	300 µm
Smallest sample, flat [radius]	13 mm
Smallest sample, convex [radius]	1,5 mm
Smallest sample, concave [radius]	80 mm
Sensor placement position	internal
Units	µm inch (mil)
Tolerance (% of [Max])	3%

Display

Display type	LCD
Display digit height	10 mm

Construction

Dimension (W×D×H)	131×65×28 mm
-------------------	--------------


KERN TC 1250-0.1F



Robust coating thickness gauge – compact and easy to use

Pictograms

STANDARD



OPTION

