

KERN CDS 30K0.1

Easy to use industrial counting scale for heavy loads, counting resolution 300.000 points, ideal for the diverse possibilities of Industry 4.0 applications



Maximum creep (30 minutes)	2 g
Default unit	kg

Display	
Display type	LCD
Display type	7 segment LED
Display backlight	✓
Display screen size	89×30 mm
Display segments	7
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction	
Dimension housing (W×D×H)	225×115×60 mm
Dimension display device (W×D×H)	225×115×60 mm
Dimensions weighing surface (W×D)	308×318 mm
Dimensions weighing surface	308×318 mm
Dimensions weighing platform (W×D×H)	308×318×75 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	metal, lacquered
Material display housing	plastic
Level indicator	✓
Wall mount	✓
Display device cable length	2,5 m

Functions	
PreTare function	✓
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	Hook (optional)
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	300.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)

Category	
Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	CDS

Measuring System	
Weighing system	Strain gauge
Weighing capacity [Max]	30 kg
Readability [d]	0,0001 kg
Reproducibility	0,0002 kg
Linearity	± 0,0005 kg
Resolution	300.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	30 kg (E2)
Possible calibration points	10 kg; 15 kg; 20 kg; 30 kg
Stabilization time	3 s
Eccentric loading at 1/3 [Max]	0,0005 kg
Construction type of the scale	Single-range balance
Units	kg g dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz ffa
Maximum creep (15 minutes)	1 g

KERN CDS 30K0.1



Easy to use industrial counting scale for heavy loads, counting resolution 300.000 points, ideal for the diverse possibilities of Industry 4.0 applications

Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
	30 sec

Auto-off interval(s) in mains power mode	off
--	-----

Tare function	manual (multi)
---------------	----------------

Number of keys for operation	7
------------------------------	---

Interface

Interfaces	RS-232 (optional)
	Ethernet (optional)
	Bluetooth BLE (v4.0) (optional)
	USB-Device (optional)
	KUP
	WiFi (optional)

compatible with EasyTouch	✓
---------------------------	---

Power Supply

Supplied power supply	Power supply unit
-----------------------	-------------------

Power supply type	Power adapter
-------------------	---------------

Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH

Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
	CH

Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
--	------------------------------

Power supply cable removable	removable
------------------------------	-----------

Input voltage device / power [Max]	5,9V, 1A
------------------------------------	----------

Power socket for mains adapter	Hollow plug, inside plus,
	Ø outside 5,5 mm, Ø inside 2,1 mm, long 13 mm

Rechargeable battery operating time - backlight on	24 h
--	------

Rechargeable battery operating time - backlight off	48 h
---	------

Rechargeable battery charging time	8 h
------------------------------------	-----

Rechargeable battery optional	Rchrg. battery optional - intern
-------------------------------	----------------------------------

Environmental conditions

Ambient temperature [Min]	-10 °C
---------------------------	--------

Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkKS calibration	963-128
--------------------------------------	---------

Article number for certificate of conformity	969-517
--	---------

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	510×380×140 mm
------------------------------	----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	8 kg
--------------------	------

Gross weight approx.	10 kg
----------------------	-------

Shipping weight	9,8 kg
-----------------	--------

Shipping volume weight	5,4 kg
------------------------	--------

Product information

GTIN/EAN number	404576 1243910
-----------------	----------------

Trade number	84238 129
--------------	-----------

REACH classification	no prohibited substances
----------------------	--------------------------

Pictograms

STANDARD



OPTION

