

# KERN CIB 10K-3

Robust counting scale with large article memory, convenient operating philosophy and checkweighing display, counting resolution up to 30,000 points



## Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	CIB

## Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	15 kg
Readability [d]	0,001 kg
Reproducibility	0,001 kg
Linearity	± 0,003 kg
Resolution	15.000
Tare range	15 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (M1)
Stabilization time	2 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,005 kg
Maximum creep (15 minutes)	4 g
Maximum creep (30 minutes)	8 g
Default unit	kg
Units	kg

## Display

Display type	LCD
Display backlight	blue, yellow, green, red
Display segments	6
Display digit height	18 mm

## Construction

Dimension housing (W×D×H)	350×330×120 mm
Dimensions weighing surface (W×D)	315×215 mm
Dimensions weighing surface	315×215 mm
Material housing	plastic
Material weighing plate	stainless steel
Level indicator	✓
Levelling feet adjustable	✓
Display device cable length	5 m

## Functions

PreTare function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Counting function	✓
Counting resolution (laboratory conditions)	30.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	500 mg
Smallest piece weight when piece counting - normal conditions	5 g
Reference quantity	n (any number of pieces)
IP protection - load cell	IP65
Tare function	manual (multi)
Number of keys for operation	34

## Power Supply

Supplied power supply	Accu & Power supply
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0.4 A max
Input voltage device / power [Max]	12 V, 1000 mA
Battery / accumulator type	Pb
Battery connection	Plug-in terminals
Rechargeable battery	6 V, 4 Ah

# KERN CIB 10K-3



Robust counting scale with large article memory, convenient operating philosophy and checkweighing display, counting resolution up to 30,000 points

Rechargeable battery operating time - backlight on 90 h

Rechargeable battery operating time - backlight off 160 h

Rechargeable battery charging time 14 h

## Environmental conditions

Ambient temperature [Min] -10 °C

Ambient temperature [Max] 40 °C

Humidity of environment [Min] 15 %

Humidity of environment [Max] 85 %

## Approval

CE mark ✓

## Services (optional)

Article number for adjustment at the location of installation 961-248

Article number for DAkkS calibration 963-128

Article number for certificate of conformity (verification) 969-517

## Packing & Shipping

Delivery time 1 d

Dimensions packaging (W×D×H) 385×400×150 mm

Shipping method Parcel service


Net weight approx. 4,0 kg

Gross weight approx. 6 kg

Shipping weight 5,184 kg

## Pictograms

### STANDARD



### OPTION

