

KERN CIB 3K-4

Robust counting scale with large article memory, convenient operating philosophy and checkweighing display, counting resolution up to 30,000 points



Category	
Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	CIB

Measuring System	
Weighing system	Strain gauge
Weighing capacity [Max]	3 kg
Readability [d]	0,0002 kg
Reproducibility	0,0002 kg
Linearity	± 0,0006 kg
Resolution	15.000
Tare range	3 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	3 kg (M1)
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,001 kg
Construction type of the scale	Single-range balance
Units	kg
Maximum creep (15 minutes)	800 mg
Maximum creep (30 minutes)	1,6 g
Default unit	kg

Display	
Display type	LCD
Display backlight	blue, yellow, green, red
Display segments	6
Display digit height	18 mm

Construction	
Dimension housing (W×D×H)	350×330×120 mm
Dimensions weighing surface (W×D)	315×215 mm
Dimensions weighing surface	315×215 mm
Material housing	plastic
Material weighing plate	stainless steel
Level indicator	✓
Levelling feet adjustable	✓
Display device cable length	5 m

Functions	
PreTare function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Counting function	✓
Counting resolution (laboratory conditions)	30.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	n (any number of pieces)
IP protection - load cell	IP65
Tare function	manual (multi)
Number of keys for operation	34

Power Supply	
Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0.4 A max
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 1000 mA
Power socket for mains adapter	Inside plus, outside minus
Battery / accumulator type	Pb

KERN CIB 3K-4

KERN

Robust counting scale with large article memory, convenient operating philosophy and checkweighing display, counting resolution up to 30,000 points

Battery connection	Plug-in terminals
Rechargeable battery	6 V, 4 Ah
Rechargeable battery operating time - backlight on	90 h
Rechargeable battery operating time - backlight off	160 h
Rechargeable battery charging time	14 h
Battery/Accu connected	fixed electrical connection, not insulated

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	15 %
Humidity of environment [Max]	85 %

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-247
Article number for DAkkS calibration	963-127
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	400×385×146 mm
Shipping method	Parcel service
Net weight approx.	3,6 kg
Gross weight approx.	4,2 kg
Shipping weight	4,5 kg
Shipping volume weight	4,5 kg

Product information

GTIN/EAN number	404576 1214880
Trade number	84238 129
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

