

# SAUTER TD 225-0.1US

Compact pocket-sized material thickness gauge

# KERN



Material housing	plastic
Cable length	0,9 m

## Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	4×1.5 V AAA
Battery capacity	1.100 mAh
Battery voltage	1,5 V

## Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	50 °C
Storage temperature [Min]	0 °C
Storage temperature [Max]	50 °C

## Approval

CE mark	✓
---------	---

## Services (optional)


Article number for factory calibration	961-113
--	---------

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	260×215×75 mm
Shipping method	Parcel service
Net weight approx.	0,20 kg
Gross weight approx.	0,75 kg
Shipping weight	0,8 kg

## Pictograms

### STANDARD



### OPTION



## Category

Brand	Sauter
Product category	Material thickness measuring device
Product group	Ultrasonic Material thickness gauge pulse-echo method
Product family	TD-US

## Measuring System

Material thickness pulse-echo [Min] (mm)	1,2 mm
Material thickness pulse-echo [Max] (mm)	225 mm
Readability material thickness [d] (mm)	0,1 mm
Speed of sound [Min] (m/s)	1000 m/s
Speed of sound [Max] (m/s)	9999 m/s
Measuring head diameter	8 mm
Measuring head measuring frequency	5 MHz
Units	mm inch
Tolerance (% of [Max])	0,5%

## Display

Display type	LCD
--------------	-----

## Construction

Dimension (W×D×H)	30×65×120 mm
Dimension housing (W×D×H)	30×65×120 mm
Dimensions completely mounted (W×D×H)	30×65×120 mm