


# KERN DS 100K0.5-2025e

Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications



## Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	DS

## Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	100 kg
Readability [d]	0,0005 kg
Reproducibility	0,0005 kg
Linearity	± 0,0015 kg
Resolution	200.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (F1)
Possible calibration points	50 kg; 100 kg
Stabilization time	3 s
Eccentric loading at 1/3 [Max]	0,0025 kg
Construction type of the scale	Single-range balance

Units	kg g dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz ffa
-------	---

Maximum creep (15 minutes)	5 g
Maximum creep (30 minutes)	10 g
Default unit	kg

## Display

Display type	LCD
Display backlight	✓
Display screen size	89×30 mm
Display digit height	21 mm
Languages of the user interface	English Symbol language

## Construction

Dimension housing (W×D×H)	225×115×60 mm
Dimension display device (W×D×H)	225×115×60 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×127 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	metal, lacquered
Material display housing	plastic
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Wall mount	✓
Display device cable length	2,5 m

## Functions

PreTare function	✓
Sum memory function	✓
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	200.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	500 mg
Smallest piece weight when piece counting - normal conditions	5 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 2 min

# KERN DS 100K0.5-2025e



Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications

	1 min
	30 min
	60 min
	30 sec

Auto-off interval(s) in mains power mode	off
--	-----

Tare function	manual (multi)
---------------	----------------

Number of keys for operation	5
------------------------------	---

## Interface

Interfaces	Ethernet (optional) analogue (4 - 20 mA) (optional) Bluetooth BLE (v4.0) (optional)
------------	---

compatible with EasyTouch	✓
---------------------------	---

## Power Supply

Supplied power supply	Power supply unit
-----------------------	-------------------

Power supply type	Power adapter
-------------------	---------------

Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH

Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
	CH

Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
--	------------------------------

Power supply cable removable	removable
------------------------------	-----------

Input voltage device / power [Max]	5,9V, 1A
------------------------------------	----------

Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 13 mm
--------------------------------	---

Battery / accumulator type	Li-Ion
----------------------------	--------

Rechargeable battery operating time - backlight on	24 h
--	------

Rechargeable battery operating time - backlight off	48 h
---	------

Rechargeable battery charging time	8 h
------------------------------------	-----

Rechargeable battery optional	Rchrg. battery optional - intern
-------------------------------	----------------------------------

## Environmental conditions

Ambient temperature [Min]	-10 °C
---------------------------	--------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Max]	80 %
-------------------------------	------

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for DAkkS calibration	963-129
--------------------------------------	---------

Article number for certificate of conformity	969-517
--	---------

## Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	930×550×210 mm
------------------------------	----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	12 kg
--------------------	-------

Gross weight approx.	13 kg
----------------------	-------

Shipping weight	21,5 kg
-----------------	---------

Shipping volume weight	21,5 kg
------------------------	---------

## Product information


GTIN/EAN number	4045761491663
-----------------	---------------

Trade number	84238220
--------------	----------

REACH classification	no prohibited substances
----------------------	--------------------------

## Pictograms

### STANDARD



### OPTION

