

# KERN DS 20K0.1

Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications



	lb
	oz
	ffa

Display	
Display type	LCD
Display backlight	✓
Display screen size	89×30 mm
Display digit height	21 mm
Languages of the user interface	English
	Symbol language

Construction	
Dimension housing (W×D×H)	225×115×60 mm
Dimensions completely mounted (W×D×H)	315×305×75 mm
Dimension display device (W×D×H)	225×115×60 mm
Dimensions weighing surface (W×D)	308×318 mm
Dimensions weighing surface	308×318 mm
Dimensions weighing platform (W×D×H)	308×318×75 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	metal, lacquered
Material display housing	Plastics
Level indicator	✓
Stand height	450 mm
Wall mount	✓
Display device cable length	2,5 m

Functions	
PreTare function	✓
Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	Hook (optional)
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	200.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	100 mg

Category	
Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	DS

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	20 kg
Readability [d]	0,0001 kg
Reproducibility	0,0001 kg
Linearity	± 0,0003 kg
Resolution	200.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	10 kg (F1); 5 kg (F1)
Possible calibration points	5 kg; 10 kg; 15 kg; 20 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,0005 kg
Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g
Default unit	kg
	kg
	g
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo

# KERN DS 20K0.1



Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications

Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min 60 min 30 sec
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	5

## Interface

Interfaces	RS-232 (optional)
	Ethernet (optional)
	Bluetooth BLE (v4.0) (optional)
	USB-Device (optional)
	KUP WiFi (optional)
EasyTouch (ET) - Compatibility	vollständig

## Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
	CH
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Humidity of environment [Max]	80 %
-------------------------------	------

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (WxDxH)	510x380x140 mm
Net weight	7,5 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	10 kg
Shipping weight	9,8 kg

## Pictograms

### STANDARD



### OPTION

